



RoadFlair

BRP390 LED56/NW 41W 220-240V DM

RoadFlair, 5624 lm, 41 W, 740 neutral white, Safety class I, Side-entry for diameter 48 to 60 mm

Designed for major and city roads, Philips RoadFlair is a new and exciting product set to brighten your streets beyond imagination. Smartly-designed to bring cities the highest savings possible with best-in-class lumen per watt, this road lighting production comes at a competitive price bound to excite. Philips RoadFlair brings energy efficiency, improves a city's sustainability drive and delivers significant cost reduction in urban environments. The right road luminaire coupled with the right lighting application will create the best environment for your municipality, benefiting local communities and boosting tourism and businesses.

Product data

General Information		Standard tilt angle side entry	
Light source replaceable	No		-
Driver included	Yes	Correlated Color Temperature (Nom)	4000 K
Light source engine type	LED	Luminous Efficacy (rated) (Nom)	140 lm/W
CE mark	CE mark	Color rendering index (CRI)	>70
Flammability mark	For mounting on normally flammable surfaces	Light source color	740 neutral white
ENEC mark	-	Optical cover type	Polycarbonate micro lens optic
Serviceability class	Class B, luminaire is equipped with some serviceable parts (when applicable): driver, control units, surge protection device, front cover and mechanical parts	Operating and Electrical	
		Input Voltage	220 to 240 V
		Line Frequency	50 or 60 Hz
		Power Consumption	41 W
		Power Factor (Fraction)	0.9
		Connection	Mains outlet socket
		Cable	Cable 0.5 m without plug
Light Technical			
Luminous Flux	5,624 lm		
Standard tilt angle posttop	-		

RoadFlair

Temperature

Ambient temperature range -40 to +50 °C

Controls and Dimming

Dimmable No

Control interface -

Mechanical and Housing

Housing Material Aluminum die cast

Optical cover material Polycarbonate

Housing Color Gray

Mounting device Side-entry for diameter 48 to 60 mm

Optical cover shape Ball, globular

Optical cover finish Frosted

Overall length 402 mm

Overall width 156 mm

Overall height 85 mm

Effective projected area 0.06 m²

Dimensions (Height x Width x Depth) 85 x 156 x 402 mm

Approval and Application

Ingress protection code IP66 [Dust penetration-protected, jet-proof]

Mech. impact protection code IK08 [5 J vandal-protected]

Protection class IEC Safety class I

Initial Performance (IEC Compliant)

Luminous flux tolerance +/-10%

Initial chromaticity (0.43, 0.40) SDCM < 5

Power consumption tolerance +/-10%

Product Data

Order product name BRP390 LED56/NW 41W 220-240V DM

Full product name BRP390 LED56/NW 41W 220-240V DM

Full product code 911401861798

Order code 911401861798

Material Nr. (12NC) 911401861798

Numerator - Quantity Per Pack 1

Numerator - Packs per outer box 1

Dimensional drawing

