

Smartbright Waterproof G3 WT068C

WT068C CW LED56 L1500 PSU

Philips Smartbright Waterproof G3 batten offers exceptional value. It is Perfect for everyday lighting installations. Available in 3 standard sizes, it has option of Standard and through wiring version.

Product data

General information		Optical cover/lens material	
Light source color	865 cool daylight	Optical cover/lens material	Polycarbonate
Optical cover/lens type	-	Optical cover/lens finish	Opal
Control interface	-	Overall length	1488 mm
Protection class IEC	Safety class II	Overall width	69 mm
CE mark	CE mark	Overall height	74 mm
Number of products on MCB of 16 A type B 1		Color	White and gray
Light source engine type	LED	Approval and application	
Operating and electrical		Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Input Voltage	220 to 240 V	Mech. impact protection code	IK06 [1 J]
Input Frequency	50 or 60 Hz	Initial performance (IEC compliant)	
Power Factor (Min)	0.9	Initial luminous flux (system flux)	5600 lm
Controls and dimming		Luminous flux tolerance	+/-10%
Dimmable	No	Initial LED luminaire efficacy	110 lm/W
Mechanical and housing		Init. Corr. Color Temperature	6500 K
Housing Material	Polycarbonate	Init. Color Rendering Index	>80
		Initial input power	51 W

Smartbright Waterproof G3 WT068C

Power consumption tolerance	+/-10%
-----------------------------	--------

Application conditions

Ambient temperature range	-20 to +45 °C
---------------------------	---------------

Product data


Full product code	871016336061499
Order product name	WT068C CW LED56 L1500 PSU
EAN/UPC - Product	8710163360614

Order code	911401881580
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	12
Material Nr. (12NC)	911401881580
Net Weight (Piece)	0.610 kg



Dimensional drawing

WT068C-5ft



WT068C CW LED56 L1500 PSU

