

# HID-HeavyDuty BHL for HPL/HPI

## BHL 250 L40-A2 230V 50Hz HD2-126

Encapsulated electromagnetic copper/iron ballasts for HPL, HPI (Plus) and SON-H lamps


### Product data

Operating and Electrical	
Input Voltage	230 V
Line Frequency	50 Hz
Input Frequency	50 Hz
Wiring	
Connector Type	Screw
Approval and Application	
Approval Marks	CE marking ENEC certificate
Product Data	
Full product code	871150091950230

Order product name	BHL 250 L40-A2 230V 50Hz HD2-126
Order code	913603920426
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6
Material Nr. (12NC)	913603920426
Full product name	BHL 250 L40-A2 230V 50Hz HD2-126
EAN/UPC - Case	8711500934604
EAN/UPC - Product/Case	8711500919502

## HID-HeavyDuty BHL for HPL/HPI

### Dimensional drawing



Product	D1	C1	A1	A2	B1
BHL 250 L40-A2 230V 50Hz	6.2 mm	66.0 mm	126.0 mm	107.5 mm	81.0 mm
HD2-126					

