



HID ignitors for series systems

SI 54 380-415V 50/60Hz

HID ignitors for series systems

Product data

General information	
Application Code	54
Lamp Type	HPI
Number of Lamps	1 piece/unit
Operating and electrical	
Input Voltage	380 to 415 V
Input Frequency	50 to 60 Hz
Igniton Type	Parallel
Number of Ignition Pulses	1
Ignition Voltage (Max)	1.5 kV
Response Voltage	330 V
Mains Voltage Performance (AC)	-8% - +6%
Mains Voltage Safety (AC)	-10% - +10%
Power Losses (Nom)	1.0 W
Wiring	
Cable Capacity Wires Device to Lamp (Nom)	120 nF
Wire Striplength	6.0 mm
Ballast Contact Wire Cross Section	0.70-2.50 mm ²
Connector Type	Screw

System characteristics	
Rated Ballast-Lamp Power	2000 W
Temperature	
T-Ambient (Max)	75 °C
T-Ambient (Min)	-20 °C
T-Storage (Max)	80 °C
T-Storage (Min)	-25 °C
T-Case Maximum (Max)	80 °C
Mechanical and housing	
Housing	SNI-115
Approval and application	
Approval Marks	CE marking ENEC certificate
Product data	
Full product code	871150091548130
Order product name	SI 54 380-415V 50/60Hz
EAN/UPC - Product	8711500915481
Order code	913619149966
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	20

HID ignitors for series systems

Material Nr. (12NC)	913619149966
Net Weight (Piece)	0.083 kg

Dimensional drawing

↕

Product	D1	C1	A1	A2	B1
SI 54 380-415V 50/60Hz	4.3 mm	38.0 mm	114.5 mm	95.0 mm	41.0 mm

SI 54 380-415V 50/60Hz

