



Gear for SDW-T lamps

CSLS 50 SDW-T 220-240V 50/60Hz

CSLS electronic control unit with impregnated (HID 'BASIC') or encapsulated (HID 'Heavy Duty') electromagnetic ballasts

Warnings and Safety

- Climatic suitability CSLS and HID BASIC: restricted to built in situations under normal conditions
- Climatic suitability CSLS and HID Heavy Duty: use in luminaires under humid conditions (not drip-proof)

Product data


General Information	
Lamp Type	SDW-T
Number of Lamps	1 piece/unit
Operating and Electrical	
Input Voltage	220 to 240 V
Input Frequency	50 to 60 Hz
Response Voltage	210 V
Mains Voltage Performance (AC)	-4%~+9%
Mains Voltage Safety (AC)	-10%~+10%
Output Peak Voltage (Max)	4500 V
Power Losses (Nom)	3.0 W
Wiring	
Cable Length From Device to Lamp	0.50 m
Wire Striplength	6.0 mm
Ballast Contact Wire Cross Section	0.50-2.50 mm ²
Cable Capacity Output Wires to Earth (Nom)	50 pF
Connector Type	Screw

System characteristics	
Rated Ballast-Lamp Power	50 W
Temperature	
T-Ambient (Max)	65 °C
T-Storage (Max)	80 °C
T-Storage (Min)	-25 °C
T-Case Lifetime (Nom)	90 °C
T-Case Maximum (Max)	90 °C
Approval and Application	
Vibration Standard	IEC68-2-6 F c
Approval Marks	CE marking VDE-EMV certificate CB Certificate
Product Data	
Full product code	871150090808730
Order product name	CSLS 50 SDW-T 220-240V 50/60Hz
EAN/UPC - Product	8711500908087
Order code	913619179966
Numerator - Quantity Per Pack	1

Gear for SDW-T lamps

Numerator - Packs per outer box	18
Material Nr. (12NC)	913619179966
Net Weight (Piece)	0.256 kg

Dimensional drawing



CSLS 50 SDW-T 220-240V 50/60Hz

Product	D1	C1	A1	A2	B1	B2
CSLS 50 SDW-T 220-240V 50/60Hz	4.5 mm	39.5 mm	98.0 mm	70.0 mm	58.5 mm	46.0 mm

