



HID ignitors for series systems

SI 51 220-240V 50/60Hz

HID ignitors for series systems

Product data

General Information	
Application Code	51
Lamp Type	HPI
Number of Lamps	1 piece/unit
Operating and Electrical	
Input Voltage	220 to 240 V
Input Frequency	50 to 60 Hz
Igniton Type	Parallel
Number of Ignition Pulses	1
Ignition Voltage (Max)	0.75 kV
Response Voltage	190 V
Mains Voltage Performance (AC)	-8% - +6%
Mains Voltage Safety (AC)	-10% - +10%
Power Losses (Nom)	1.0 W
Wiring	
Cable Capacity Wires Device to Lamp (Nom)	150 nF
Wire Striplength	6.0 mm
Ballast Contact Wire Cross Section	0.70-2.50 mm ²
Connector Type	Screw

System characteristics	
Rated Ballast-Lamp Power	250/400 W
Temperature	
T-Ambient (Max)	75 °C
T-Ambient (Min)	-20 °C
T-Storage (Max)	80 °C
T-Storage (Min)	-25 °C
T-Case Maximum (Max)	80 °C
Mechanical and Housing	
Housing	SNI-85
Approval and Application	
Approval Marks	CE marking ENEC certificate
Product Data	
Full product code	871150091553530
Order product name	SI 51 220-240V 50/60Hz
EAN/UPC - Product	8711500915535
Order code	913619519966
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	48

HID ignitors for series systems

Material Nr. (12NC)	913619519966
Net Weight (Piece)	0.047 kg

Dimensional drawing

31

Product	D1	C1	A1	A2	B1
SI 51 220-240V 50/60Hz	4.3 mm	38.0 mm	84.5 mm	65.0 mm	41.0 mm

SI 51 220-240V 50/60Hz

