



HID-Constant wattage BSX for SOX

BSX 55 H26 220-230V 50Hz CW-173/44

Constant-wattage (potted) electromagnetic copper/iron ballasts for use with an external ignitor for SOX and SOX-E lamps

Product data

| General Information | |
|------------------------------------|-----------------------------|
| Application Code | H26 |
| Design | CW-173/44 |
| Lamp Type | SOX-E |
| Number of Lamps | 1 piece/unit |
| Operating and Electrical | |
| Input Voltage | 220 to 230 V |
| Input Frequency | 50 Hz |
| Mains Voltage Performance (AC) | -8%+6% |
| Mains Voltage Safety (AC) | -10%+10% |
| Power Losses (Nom) | 19.5 W |
| Wiring | |
| Wire Striplength | 6.0 mm |
| Ballast Contact Wire Cross Section | 0.75-2.50 mm ² |
| Connector Type | Screw |
| System characteristics | |
| Capacitor | 4.4µF/5.7µF/380V |
| Rated Ballast-Lamp Power | 55 W |
| Recommended Ignitor | ignitor SX72 (913654059066) |

| Temperature | |
|---------------------------|--------|
| T-Storage (Max) | 80 °C |
| T-Storage (Min) | -25 °C |
| T-Winding (Max) | 130 °C |
| Delta-T Normal Conditions | 70 °C |

| Approval and Application | |
|--------------------------|-----------------------------|
| Approval Marks | CE marking ENEC certificate |

| Product Data | |
|---------------------------------|------------------------------------|
| Full product code | 871150091996099 |
| Order product name | BSX 55 H26 220-230V 50Hz CW-173/44 |
| EAN/UPC - Product | 8711500919960 |
| Order code | 913653000326 |
| Numerator - Quantity Per Pack | 1 |
| Numerator - Packs per outer box | 12 |
| Material Nr. (12NC) | 913653000326 |
| Net Weight (Piece) | 1.700 kg |

HID-Constant wattage BSX for SOX

Dimensional drawing

Δ 1

| Product | D1 | C1 | A1 | A2 | B1 | B2 |
|--|--------|---------|----------|----------|---------|---------|
| BSX 55 H26 220-230V 50Hz CW-173/44 | 4.2 mm | 44.0 mm | 173.0 mm | 157.0 mm | 64.0 mm | 42.0 mm |

BSX 55 H26 220-230V 50Hz CW-173/44

