



# HID ignitors for series systems

## SND 57 220-240V 50/60Hz

HID ignitors for series systems


### Product data

General information	
Application Code	57
Lamp Type	SON
Number of Lamps	1 piece/unit
Operating and electrical	
Input Voltage	220 to 240 V
Input Frequency	50 to 60 Hz
Igniton Type	Semi-Parallel
Ignition Attempts	3
Ignition Time (Max)	1185 s
Ignition Voltage (Max)	2.5 kV
Ignition Voltage (Min)	1.8 kV
Response Voltage	195 V
Mains Voltage Performance (AC)	-8% - +6%
Mains Voltage Safety (AC)	-10% - +10%
Power Losses (Nom)	1.0 W
Wiring	
Ballast Contact Wire Cross Section	0.70-2.50 mm <sup>2</sup>
Connector Type	Screw
System characteristics	
Rated Ballast-Lamp Power	50/70 W

Temperature	
T-Ambient (Max)	85 °C
T-Ambient (Min)	-20 °C
T-Case Maximum (Max)	90 °C
Mechanical and housing	
Housing	SNI-85
Approval and application	
Approval Marks	CE marking ENEC certificate
Product data	
Full product code	871150093066830
Order product name	SND 57 220-240V 50/60Hz
EAN/UPC - Product	8711500930668
Order code	913700184966
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	48
Material Nr. (12NC)	913700184966
Copy Net Weight (Piece)	0.050 kg

## HID ignitors for series systems

### Dimensional drawing



Product	D1	C1	A1	A2	B1
SND 57 220-240V 50/60Hz	4.3 mm	38.5 mm	84.5 mm	65.0 mm	41.5 mm

SND 57 220-240V 50/60Hz

