



HF-Matchbox Red

HF-M RED 114 SH TL/TL5/PL-C/S 230-240V

HF-Matchbox Red is an affordable, reliable, compact, lightweight and high-frequency ballast for use with system wattages below 25 W in combination with TL mini, TL-D, TL5 and TL5c, PL-T/C, and PL-L/S lamps. The HF-M Red range has a robust design, meets all relevant international safety and performance standards and has an energy efficiency index (CELMA EEI) of A2. The ballast is primarily designed for Indoor application. For outdoor application, the luminaire should be minimum Classland need to be sufficiently protected against water & dust. The installation should also be guard against any lightening surge or any other necessary electrical protection as deemed in such typical installation & application.

Product data

General information	
Lamp Type	TL/TL5/PL-C/S
Number of Lamps	1 piece/unit
Number of Products on MCB (16A Type B) (Nom)	101
Automatic Restart	Yes
Operating and electrical	
Input Voltage	230 to 240 V
Input Frequency	50 to 60 Hz
Power Factor 100% Load (Nom)	0.64
Ignition Time (Max)	1.55 s
Mains Voltage Performance (AC)	-8%~+6%
Mains Voltage Safety (AC)	-10%~+10%
Power Losses (Nom)	2.9 W
Efficiency at full load [%]	83.7 %

Wiring	
Connector Type Input Terminals	Insert
Color Input Terminals	Blue
Color Output Terminals	Grey
Connector Type Output Terminals	Insert
Cable Length Hot Wiring	0.75 m
Wire Striplength	8.0-9.0 mm
Input Terminal Cross Section	0.50-1.50 mm ²
Output Terminal Cross Section	0.50-1.50 mm ²

System characteristics	
Rated Ballast-Lamp Power	14 W
Rated Lamp Power on TL5	14 W
System Power on TL5	16 W
Lamp Power on TL5	13.1 W
Power Loss on TL5	2.9 W
System Power on PL-C	10.6 W
Rated Lamp Power on PL-C	14 W

HF-Matchbox Red

Power Loss on PL-C	1.7 W
Lamp Power on PL-C	8.9 W
Temperature	
T-Ambient (Max)	50 °C
T-Ambient (Min)	-25 °C
T-Case Maximum (Max)	80 °C
Mechanical and housing	
Housing	SH
Emergency operation	
Battery Voltage Lamp Ignition	190-254 V
Approval and application	
IP Classification	IP20 [Finger-protected]

Approval Marks	CE marking ENEC certificate
Product data	
Full product code	871150093140530
Order product name	HF-M RED 114 SH TL/TL5/PL-C/S 230-240V
EAN/UPC - Product	8711500931405
Order code	913700423266
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	50
Material Nr. (12NC)	913700423266
Net Weight (Piece)	0.034 kg

Dimensional drawing



Product	D1	C1	C2	A1	A2	B1
HF-M RED 114 SH TL/TL5/PL-C/S 230-240V	4.2 mm	22.0 mm	10.0 mm	80.0 mm	70.0 mm	40.0 mm

HF-M RED 114 SH TL/TL5/PL-C/S 230-240V

