


PHILIPS

Lighting



PrimaVision Compact for CDM

HID-PV C 70 /P CDM 220-240V 50/60Hz

High-quality, compact and lightweight HID electronic gear for optimal and reliable performance of 20, 35, 50 and 70 W CDM lamps

Product data

General information

Type Version	Gen 4.3
Lamp Type	CDM
Number of Lamps	1 piece/unit
Suitable For Outdoor Use	No
Number of Products on MCB (16A Type B) (Nom)	20
Automatic Restart	Yes

Operating and electrical

Input Voltage	220 to 240 V
Input Frequency	50 to 60 Hz
Operating Frequency (Nom)	0.14 kHz
Power Factor 100% Load (Nom)	0.95
Ignition Voltage (Max)	4.0 kV
Ignition Switch-Off Time (Nom)	18 min
Mains Voltage Performance (AC)	-10%~+6%
Mains Voltage Safety (AC)	-18%~+10%
Earth Leakage Current (Max)	0.25 mA
Inrush Current Width	0.33 ms
Constant Wattage Deviation	-3%/+3%
Power Losses (Nom)	7.0 W

Inrush Current Peak (Max)	33 A
Efficiency at full load [%]	90.6 %

Wiring

Cable Capacity Output Wires Mutual (Nom)	100 pF
Cable Length From Device to Lamp	1.5 m
Ballast Contact Wire Cross Section	0.50-2.50 mm ²
Connector Type	Insert

System characteristics

Rated Ballast-Lamp Power	70 W
--------------------------	------

Temperature


T-Ambient (Max)	50 °C
T-Ambient (Min)	-20 °C
T-Storage (Max)	80 °C
T-Storage (Min)	-25 °C
T-Case Lifetime (Nom)	80 °C
T-Case Maximum (Max)	80 °C

PrimaVision Compact for CDM

Mechanical and housing	
Housing	/P
Approval and application	
Active Temperature Protection	Yes
EMI 9 kHz ... 300 MHz	CISPR 15 ed 7.2
Safety Standard	EN 61347-2-12
Quality Standard	ISO 9000:2000
Environmental Standard	ISO 14001
Harmonic Current Emission Standard	EN 61000-3-2
EMC Immunity Standard	EN 61547
Vibration Standard	IEC68-2-6 F c
Bumps Standard	IEC 68-2-29 Eb
Humidity Standard	IEC 928-13
Approval Marks	CE marking ENEC certificate

Hum And Noise Level	37 dB(A)
Product data	
Full product code	872790086553000
Order product name	HID-PV C 70 /P CDM 220-240V 50/60Hz
EAN/UPC - Product	8711500998231
Order code	913700653066
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	12
Material Nr. (12NC)	913700653066
Copy Net Weight (Piece)	0.210 kg

Dimensional drawing



HID-PV C 70 /P CDM 220-240V 50/60Hz

Product	D1	C1	A1	A2	B1	B2
HID-PV C 70 /P CDM 220-240V 50/60Hz	4.9 mm	29.6	106.6	98.5	71.6	63.7
		mm	mm	mm	mm	mm

