



# PrimaVision Compact for CDM

## HID-PV C 35 /I CDM 220-240V 50/60Hz NG

High-quality, compact and lightweight HID electronic gear for optimal and reliable performance of 20, 35, 50 and 70 W CDM lamps

### Product data

General Information		Inrush Current Peak (Max)	
Type Version	ng		26 A
Lamp Type	CDM	Wiring	
Number of Lamps	1 piece/unit	Cable Capacity Output Wires Mutual (Nom)	150 pF
Suitable For Outdoor Use	No	Cable Length From Device to Lamp	2.0 m
Number of Products on MCB (16A Type B) (Nom)	24	Ballast Contact Wire Cross Section	0.50-2.50 mm <sup>2</sup>
Automatic Restart	Yes	Connector Type	Insert
Operating and Electrical		System characteristics	
Input Voltage	220 to 240 V	Rated Ballast-Lamp Power	35 W
Input Frequency	50 to 60 Hz	Temperature	
Operating Frequency (Nom)	0.14 kHz	T-Ambient (Max)	50 °C
Power Factor 100% Load (Nom)	0.95	T-Ambient (Min)	-20 °C
Ignition Voltage (Max)	4.0 kV	T-Storage (Max)	75 °C
Ignition Switch-Off Time (Nom)	18 min	T-Storage (Min)	-25 °C
Mains Voltage Performance (AC)	-10%+6%	T-Case Lifetime (Nom)	75 °C
Mains Voltage Safety (AC)	-18%+10%	T-Case Maximum (Max)	75 °C
Earth Leakage Current (Max)	0.25 mA	Mechanical and Housing	
Inrush Current Width	0.25 ms	Housing	/I
Constant Wattage Deviation	-3%/+3%		
Power Losses (Nom)	4.5 W		

# PrimaVision Compact for CDM

## Approval and Application

Active Temperature Protection	Yes
EMI 9 kHz ... 300 MHz	CISPR 15 ed 7.2
Safety Standard	EN 61347-2-12
Quality Standard	ISO 9000:2000
Environmental Standard	ISO 14001
Harmonic Current Emission Standard	EN 61000-3-2
EMC Immunity Standard	EN 61547
Vibration Standard	IEC68-2-6 F c
Bumps Standard	IEC 68-2-29 Eb
Humidity Standard	IEC 928-13
Approval Marks	CE marking ENEC certificate
Temperature Marking	F
Hum And Noise Level	37 dB(A)

## Product Data

Full product code	872790085973700
Order product name	HID-PV C 35 /I CDM 220-240V 50/60Hz NG
EAN/UPC - Product	8711500881700
Order code	913700653166
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	12
Material Nr. (12NC)	913700653166
Net Weight (Piece)	0.360 kg

## Dimensional drawing

Λ?

Product	D1	C1	A1	A2	B1
HID-PV C 35 /I CDM 220-240V 50/60Hz NG	4.8 mm	34.5 mm	188.0 mm	170.0 mm	82.7 mm

HID-PV C 35 /I CDM 220-240V 50/60Hz NG

