



DynaVision Programmable Xtreme for CPO

HID-DV PROG Xt 140 CPO C1 208-277V

Highly reliable and flexible electronic drivers for CPO lamps; designed to save on energy costs via integrated controls and to reduce maintenance costs thanks to 80,000-hour lifetime and integrated lightning protection. The DynaVision Programmable product family is the perfect basis for any sort of lighting management solution.

Product data

General information			
Type Version	-	Ignition Switch-Off Time (Max)	20 min
Lamp Type	CPO	Mains Voltage Performance (AC)	188-305V
Number of Lamps	1 piece/unit	Mains Voltage Safety (AC)	160-305V
Suitable For Outdoor Use	Yes	Power Factor 50% Load (Min)	0.98
Number of Products on MCB (16A Type B) (Nom)	5	Earth Leakage Current (Max)	0.7 mA
Default Lamp Selected	CPO140	Output Peak Voltage (Max)	250 V
Automatic Restart	Yes	Inrush Current Width	0.47 ms
		Lamp Power Tolerance	-3%/+3%
		Input Current (Nom)	0.75 A
		Inrush Current Peak (Max)	52 A
		Efficiency at full load [%]	90.78 %
Operating and electrical		Wiring	
Input Voltage	208-240-277 V	Cable Capacity Output Wires Mutual (Nom)	1000 pF
Input Frequency	50 to 60 Hz	Cable Length From Device to Lamp	10 m
Minimum Mains Voltage Operation (Min)	172 V	Wire Striplength	10.0-11.0 mm
Operating Frequency (Nom)	0.40 kHz	Ballast Contact Wire Cross Section	0.50-2.50 mm ²
Power Factor 100% Load (Nom)	0.99		
Ignition Voltage (Max)	5 kV		

DynaVision Programmable Xtreme for CPO

Connector Type	WAGO series 804
----------------	-----------------

System characteristics

Rated Ballast-Lamp Power	140 W
Rated Lamp Power on CPO	140 W
System Power on CPO	153 W
Lamp Power on CPO	140 W
Power Loss on CPO	13 W
Power Loss on CPO While Dimming	7 W

Temperature

T-Ambient (Max)	50 °C
T-Ambient (Min)	-30 °C
T-Storage (Max)	50 °C
T-Storage (Min)	-30 °C
T-Case Lifetime (Nom)	80 °C
T-Case Switch Off (Min)	92 °C

Controls and dimming

Control Interface	PROG
Programmable Lamp Settings	CPO140/SON150/CDO150
Pre-Set Integrated Controls	Dali
Programmable Dimming Options	ALO/CLO/Dynadimmer/Linesitch/ AmpDim
Run-Up Time Before Dimming	5 min
Fade Down Rate	0.5 %/sec
Fade Up Rate	6.3 %/sec
Control Input Protection	Yes (Basic insulation)
Regulating Level	50%-100%

Mechanical and housing

Housing	C1
---------	----

Approval and application

Surge Protection (Common/Differential)	EN61547 (L-L 2kV, L-G 4kV), 10 kV TIL
IP Classification Luminaire	34
Active Temperature Protection	Yes
EMI 9 kHz ... 300 MHz	CISPR 15 ed 7.2
EMI 30 MHz ... 1000 MHz	-
Safety Standard	IEC 607, 609, 926, 928 [No Standard for HID Lamp drivers exists. Requirements in these standards to be used if considered relevant for the product.]
Quality Standard	ISO 9000:2000
Environmental Standard	ISO 14001
Harmonic Current Emission Standard	IEC 61000-3-2
Vibration Standard	IEC 68-2-6 Fc (10-150Hz, 2G)
Bumps Standard	IEC 68-2-29 Eb (10G/16ms)
Humidity Standard	EN 61347-2-12 clause 11
Approval Marks	F-Marking CE marking ENEC certificate VDE-EMV certificate
Hum And Noise Level	< 30 dB(A)

Product data

Full product code	871829120457200
Order product name	HID-DV PROG Xt 140 CPO C1 208-277V
EAN/UPC - Product	8718291204572
Order code	913700675266
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	12
Material Nr. (12NC)	913700675266
Net Weight (Piece)	0.950 kg

Dimensional drawing

A2

Product	D1	C1	A1	A2	B1	B2
HID-DV PROG Xt 140	5.0 mm	65.0	150.0	135.9	65.0	46.8
CPO C1 208-277V		mm	mm	mm	mm	mm

HID-DV PROG Xt 140 CPO C1 208-277V

DynaVision Programmable Xtreme for CPO

