

# HID-Basic BSN/BMH MK4 semi-parallel for SON/CDO/CDM/MH/ HPI

## BSN 100 K302-A2-ITS 230V 50Hz



Impregnated electromagnetic copper ballasts for use with an external semi-parallel ignitor for CDM, CDO, MH, HPI (Plus) and SON lamps

### Product data

Operating and Electrical		Order product name	
Input Voltage	230 V		BSN 100 K302-A2-ITS 230V 50Hz
Line Frequency	50 Hz	Order code	913700752326
Input Frequency	50 Hz	Numerator - Quantity Per Pack	1
		Numerator - Packs per outer box	6
		Material Nr. (12NC)	913700752326
Wiring		Full product name	BSN 100 K302-A2-ITS 230V 50Hz
Connector Type	Screw	EAN/UPC - Case	8718696740873
		EAN/UPC - Product/Case	8718696740866
Approval and Application			
Approval Marks	CE marking ENEC certificate		
Product Data			
Full product code	871869674086600		

# HID-Basic BSN/BMH MK4 semi-parallel for SON/CDO/CDM/MH/HPI

## Dimensional drawing



Product	A1	A2	B1	C1	D1
BSN 100 K302-A2-ITS 230V 50Hz	123 mm	98 mm	61 mm	52 mm	6.2 mm

