



HID-HeavyDuty BSN semi-parallel for SON/CDO/MH/HPI

BSN 150 L33-A2-TS 230V 50Hz



Encapsulated electromagnetic copper/iron ballasts for use with an external semi-parallel ignitor for CDM, CDO, MH, HPI (Plus) and SON lamps

Product data

Operating and Electrical		Order product name	
Input Voltage	230 V	Order product name	BSN 150 L33-A2-TS 230V 50Hz
Line Frequency	50 Hz	Order code	913700752826
Input Frequency	50 Hz	Numerator - Quantity Per Pack	1
		Numerator - Packs per outer box	6
		Material Nr. (12NC)	913700752826
		Full product name	BSN 150 L33-A2-TS 230V 50Hz
		EAN/UPC - Case	8718696741016
		EAN/UPC - Product/Case	8718696741009
Wiring			
Connector Type	Screw		
Approval and Application			
Approval Marks	CE marking ENEC certificate		
Product Data			
Full product code	871869674100900		

HID-HeavyDuty BSN semi-parallel for SON/CDO/MH/HPI

Dimensional drawing



Product	A1	A2	B1	C1	D1
BSN 150 L33-A2-TS 230V 50Hz	126 mm	108 mm	81 mm	66 mm	6.2 mm

