

# HID-Basic Gearbox system for SON (India)

## BSN 070 M261

Impregnated electromagnetic ballasts of copper and steel construction for use in combination with an external ignitor for High-Pressure Sodium Vapor (SON) lamps

### Warnings and Safety

- Ballasts are only suitable for use with integrated luminaires

### Product data


General Information		Wiring	
Application Code	070 M261	Connector Type	Screw
Lamp Type	SON		
Number of Lamps	1 piece/unit	System characteristics	
		Rated Ballast-Lamp Power	70 W
Operating and Electrical		Temperature	
Input Voltage	220/240 V	T-Winding (Max)	130 °C
Input Frequency	50 Hz	Delta-T Normal Conditions	70 °C
Mains Voltage Performance (AC)	240+6%--8%		
Mains Voltage Safety (AC)	240-10%--10%	Approval and Application	
Input Current with PF Correction	0.41 A	Energy Efficiency Index	Not specified
Input Current without PF Correction	1.00 A	Approval Marks	CE marking
Power Factor with PF Compensation	0.85		
Power Factor without PF Compensation (Nom)	0.35	Product Data	
Power Losses (Nom)	15 W	Full product code	871150088440400
		Order product name	BSN 070 M261

## HID-Basic Gearbox system for SON (India)

EAN/UPC - Product	8711500884404
Order code	913702251012
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	12

Material Nr. (12NC)	913702251012
Net Weight (Piece)	1.050 kg

### Dimensional drawing



Product	D1	C1	A1	A2	B1
BSN 070 M261	6.3 mm	51.0 mm	117.0 mm	98.0 mm	60.0 mm

BSN 070 M261

