



HID-Basic Semi-Parallel ballasts for SON/CDM/MH lamps

BSN 400L 300I TS

The HID Basic Semi-Parallel ballast is an impregnated (HID standard) electromagnetic copper/iron ballast for use with an external ignitor for HID lamps.

Product data

General Information		Temperature	
Application Code	L300 ITS	T-Winding (Max)	130 °C
		Delta-T Normal Conditions	65 °C
Operating and Electrical		Approval and Application	
Input Voltage	220 V	Approval Marks	CCC certificate
Input Frequency	50 Hz		
Power Factor 100% Load (Min)	0.85	Product Data	
Mains Voltage Performance (AC)	-8%~+6%	Full product code	694818229950500
Mains Voltage Safety (AC)	-10%~+10%	Order product name	BSN 400L 300I TS
Input Current with PF Correction	2.4 A	EAN/UPC - Product	6948182295460
Input Current without PF Correction	4.45 A	Order code	913710109542
Power Factor without PF Compensation (Nom)	0.45	Numerator - Quantity Per Pack	1
Power Losses (Nom)	26.5 W	Numerator - Packs per outer box	4
Wiring		Material Nr. (12NC)	913710109542
Connector Type	Screw	Net Weight (Piece)	4.500 kg
System characteristics			
Rated Ballast-Lamp Power	400 W		

HID-Basic Semi-Parallel ballasts for SON/CDM/MH lamps

Dimensional drawing



Product	D1	C1	A1	A2	B1
BSN 400L 300I TS	6.2 mm	82 mm	165.0 mm	150 mm	96.5 mm

BSN 400 L300 ITS

