

# HID-Basic ballasts for HPL and HPI(PLUS) lamps

## BHLE 400L 202

The HID-Basic ballast is an impregnated (HID standard) electromagnetic ballast for HID lamps, for use in combination with an external ignitor.


### Product data

General Information	
Application Code	L202
Operating and Electrical	
Input Voltage	230 V
Input Frequency	50 Hz
Power Factor 100% Load (Min)	0.85
Mains Voltage Performance (AC)	-8% - +6%
Mains Voltage Safety (AC)	-10% - +10%
Input Current with PF Correction	2.15 A
Input Current without PF Correction	3.25/3.4 A
Power Factor without PF Compensation (Nom)	0.60
Power Losses (Nom)	27.5/30.5 W
Wiring	
Connector Type	Screw
System characteristics	
Rated Ballast-Lamp Power	400 W

Temperature	
T-Winding (Max)	130 °C
Delta-T Normal Conditions	70/75 °C
Approval and Application	
Approval Marks	CE marking
Product Data	
Full product code	872790084180000
Order product name	BHLE 400L 202
EAN/UPC - Product	8711500997913
Order code	913713017650
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6
Material Nr. (12NC)	913713017650
Net Weight (Piece)	3.140 kg

## HID-Basic ballasts for HPL and HPI(PLUS) lamps

### Dimensional drawing



Product	D1	C1	A1	A2	B1
BHLE 400L 202	6.2 mm	64.5 mm	165.0 mm	144.0 mm	75.5 mm

BHLE 400 L202

