

# HID-Basic Semi-Parallel ballasts for SON/CDM/MH lamps

## BSNE 150L 300I TS

The HID Basic Semi-Parallel ballast is an impregnated (HID standard) electromagnetic copper/iron ballast for use with an external ignitor for HID lamps.


### Product data

General information	
Application Code	L300 ITS
Operating and electrical	
Input Voltage	220 V
Input Frequency	50 Hz
Power Factor 100% Load (Min)	0.45
Mains Voltage Performance (AC)	-8%~+6%
Mains Voltage Safety (AC)	-10%~+10%
Input Current with PF Correction	0.85 A
Input Current without PF Correction	1.8 A
Power Factor without PF Compensation (Nom)	0.85
Power Losses (Nom)	20 W
Wiring	
Connector Type	Screw
System characteristics	
Rated Ballast-Lamp Power	150 W

Temperature	
T-Winding (Max)	130 °C
Delta-T Normal Conditions	70 °C
Approval and application	
Approval Marks	CE marking CCC certificate
Product data	
Full product code	697480505033800
Order product name	BSNE 150L 300I TS
EAN/UPC - Product	6974805050338
Order code	913713019359
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6
Material Nr. (12NC)	913713019359
Copy Net Weight (Piece)	1.730 kg

## HID-Basic Semi-Parallel ballasts for SON/CDM/MH lamps

### Dimensional drawing



BSNE 150L 300I TS

Product	D1	C1	A1	A2	B1
BSNE 150L 300I TS	6.3 mm	64.5 mm	120.0 mm	99.0 mm	75.0 mm

