



# HF-Selectalume II for TL5 lamps

## HF-S 235 TL5 II 220-240V 50/60Hz

HF-Selectalume II TL5 is the most cost-effective, reliable and outstanding solution for fluorescent lamps. These ballasts are part of an overall high-efficiency lighting system that may help you or your customers to achieve any international or local energy code you need to comply with. HF-Selectalume II TL5 ballasts are the ideal choice for a broad range of new construction and retrofit applications within the commercial sector, including general surface mounting or office lighting, parking garages, warehouses, waterproof and other applications. The ballast is primarily designed for Indoor application. For outdoor application, the luminaire should be minimum Classland need to be sufficiently protected against water & dust. The installation should also be guard against any lightening surge or any other necessary electrical protection as deemed in such typical installation & application.

### Product data


Operating and Electrical		T-Case Lifetime (Nom)	75 °C
Input Voltage	220 to 240 V	T-Case Maximum (Max)	75 °C
Line Frequency	50 to 60 Hz	<b>Mechanical and Housing</b>	
Input Frequency	50 to 60 Hz	Housing	L 280x30x21.5
Earth Leakage Current (Max)	0.5 mA	<b>Approval and Application</b>	
Inrush Current Width	0.25 ms	Ingress protection code	IP20 [Finger-protected]
Inrush Current Peak (Max)	25 A	Energy Efficiency Index	A2
<b>Wiring</b>		Approval Marks	F-Marking CE marking ENEC certificate CCC certificate C-Tick certificate PSB certification TISI marking SIRIM approval CB Certificate CCC certificate VDE-EMV certificate
Connector Type Input Terminals	WAGO 744 connector		
Connector Type Output Terminals	WAGO 744 connector [Suitable for manual wiring]		
<b>Temperature</b>			
Ambient temperature range	-15 °C to 50 °C		

## HF-Selectalume II for TL5 lamps

Product Data	
Full product code	872790088334300
Order product name	HF-S 235 TL5 II 220-240V 50/60Hz
Order code	913713033366
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	12

Material Nr. (12NC)	913713033366
Full product name	HF-S 235 TL5 II 220-240V 50/60Hz
EAN/UPC - Case	8727900883343
EAN/UPC - Product/Case	8711500998699

### Dimensional drawing



Product
HF-S 235 TL5 II 220-240V 50/60Hz

Product	A1	B1	C1	A2	B2	D1
HF-S 235 TL5 II 220-240V 50/60Hz	280 mm	30 mm	21.5 mm	265 mm		4.2 mm

