

# HID-Basic Semi-Parallel Economic ballasts for SON/CDM/MH lamps

## BSNE 150L 301I TS

The HID Basic Semi-Parallel ballast is an impregnated (HID standard) electromagnetic copper/iron ballast for use with an external ignitor for HID lamps.

### Product data

General Information	
Application Code	L301 ITS
Design	-
Operating and Electrical	
Input Voltage	220 V
Input Frequency	50 Hz
Power Factor 100% Load (Min)	0.85
Mains Voltage Performance (AC)	-8% - +6%
Mains Voltage Safety (AC)	-10% - +10%
Input Current with PF Correction	0.85 A
Input Current without PF Correction	1.8 A
Power Factor without PF Compensation (Nom)	0.45
Power Losses (Nom)	10.5 W


Wiring	
Connector Type	Screw
System characteristics	
Rated Ballast-Lamp Power	150 W
Temperature	
T-Winding (Max)	130 °C
Delta-T Normal Conditions	70 °C
Approval and Application	
Approval Marks	CE marking
Product Data	
Full product code	871829112574700
Order product name	BSNE 150L 301I TS
EAN/UPC - Product	8718291125747

## HID-Basic Semi-Parallel Economic ballasts for SON/CDM/MH lamps

Order code	913713202450
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6
Material Nr. (12NC)	913713202450

Net Weight (Piece)	1.570 kg
--------------------	----------

### Dimensional drawing



Product	C1	A1	B1
BSNE 150L 301I TS	64.5 mm	120.0 mm	72.5 mm

BSNE 150 L301 ITS

