



Standard Extra Low Voltage A60

Stan ELV 40W E27/BRC 24V A60 CL 1CT

Clear lamp (A-bulb) for operation on voltages of 12, 24, 42 and 50 V

Product data

General Information	
Cap-Base	E27 [E27]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	1,000 hour(s)
Switching Cycle	4,000
Rated Lifetime (Hours)	1,000 hour(s)
Lighting Technology	Incandescent

Light Technical	
Luminous Flux	580 lumen
Correlated Color Temperature (Nom)	2700 K
Color rendering index (CRI)	100

Operating and Electrical	
Power Consumption	40 W
Starting Time (Nom)	0.0 s
Warm-up time to 60% light	instant full light s
Voltage (Nom)	24 V
Voltage (Nom)	24 V

Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	A60 [A 60mm]

Approval and Application	
Energy Consumption kWh/1000 h	40 kWh

Product Data	
Full product code	871150002293684
Order product name	Stan ELV 40W E27/BRC 24V A60 CL 1CT
Order code	920011020503
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	120
Material Nr. (12NC)	920011020503
Full product name	Stan ELV 40W E27/BRC 24V A60 CL 1CT
EAN/UPC - Case	8711500348906

Standard Extra Low Voltage A60

Dimensional drawing

Product	D (max)	C (max)
Stan ELV 40W E27/BRC 24V A60 CL 1CT	60 mm	107.5 mm

