



# Standard Extra Low Voltage A60

## Stan ELV 60W E27/BRC 50V A60 CL 1CT

Clear lamp (A-bulb) for operation on voltages of 12, 24, 42 and 50 V

### Product data

General Information	
Cap-Base	E27 [E27]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	1,000 hour(s)
Switching Cycle	4,000
Rated Lifetime (Hours)	1,000 hour(s)
Lighting Technology	Incandescent

  

Light Technical	
Luminous Flux	810 lumen
Correlated Color Temperature (Nom)	2700 K
Color rendering index (CRI)	100

  

Operating and Electrical	
Power Consumption	60.0 W
Starting Time (Nom)	0.0 s
Warm-up time to 60% light	instant full light s
Voltage (Nom)	50 V
Voltage (Nom)	50 V

  

Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	A60 [A 60mm]

  

Approval and Application	
Energy Consumption kWh/1000 h	60 kWh

  

Product Data	
Full product code	871150010188484
Order product name	Stan ELV 60W E27/BRC 50V A60 CL 1CT
Order code	920021025303
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	120
Material Nr. (12NC)	920021025303
Full product name	Stan ELV 60W E27/BRC 50V A60 CL 1CT
EAN/UPC - Case	8711500348999
EAN/UPC - Product/Case	8711500101884

## Standard Extra Low Voltage A60

### Dimensional drawing

Product	D (max)	C (max)
Stan ELV 60W E27/BRC 50V A60 CL 1CT	60 mm	107.5 mm

