



Halogen non-reflector

7388 20W G4 6V 1CT/10X10F

Halogen non-reflector lamps offer high-quality light and are easy to install, replace and operate. All halogen non-reflector lamps incorporate a distortion-free quartz bulb and a precise positioning of the mounted filament. These ensure optimal beam performance and consistent, high light output. A wide range of wattages is available for a broad variety of applications, including projection systems. In addition you get all the proven advantages of halogen technology such as a full spectrum and a color rendering index (CRI) of 100 – the same as natural light and the best that it can be. Halogen lamps also create a comfortable warm white light, and they maintain their lumen output, with almost no reduction, throughout their lifetime.

Product data

Operating and Electrical	
Power Consumption	20 W
Voltage (Nom)	6 V
Voltage (Nom)	6 V

General Information	
Cap-Base	G4 [G4]
Operating Position	UNIVERSAL [Any or Universal (U)]


Light Technical	
Luminous Flux	460 lumen
Color rendering index (CRI)	100

Mechanical and Housing	
Bulb Material	Quartz-UV Open

Product Data	
Full product code	871150040986750
Order product name	7388 20W G4 6V 1CT/10X10F
Order code	923874610103
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	100
Material number (12NC)	923874610103
Full product name	7388 20W G4 6V 1CT/10X10F
EAN/UPC - Case	8711500423306

Halogen non-reflector

Dimensional drawing



Product	D (max)	L (max)	C (max)
7388 20W G4 6V 1CT/10X10F	9.5 mm	19.75 mm	31 mm

