



# Halogen Clickline G9



## Halogen MV Click 18W G9 230V CL 1CT

Ideal solution for small decorative luminaires. UV-block glass and safety fuse allow usage without cover glass. The compact Clickline gives crisp white light over a long lifetime.

### Product data

General Information	
Cap-Base	G9 [G9]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	2,000 hour(s)
Switching Cycle	8,000
Rated Lifetime (Hours)	2,000 hour(s)
Lighting Technology	Halogen
Flux measurement reference	Sphere

Light Technical	
Luminous Flux	195 lm
Chromaticity Coordinate X (Nom)	0.452
Chromaticity Coordinate Y (Nom)	0.409
Correlated Color Temperature (Nom)	2800 K
Luminous Efficacy (rated) (Nom)	11.1 lm/W
Color rendering index (CRI)	100

Operating and Electrical	
Power Consumption	19 W
Lamp Current (Nom)	0.08 A
Starting Time (Nom)	0.0 s
Warm-up time to 60% light	instant full light s
Power Factor (Fraction)	1
Voltage (Nom)	230 V

Voltage (Nom)	230 V
---------------	-------

Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	T13 [T 13 mm]


Approval and Application	
Energy Efficiency Class	G
Energy Consumption kWh/1000 h	19 kWh
EPREL Registration Number	423243

Product Data	
Order product name	Halogen MV Click 18W G9 230V CL 1CT
Full product name	Halogen MV Click 18W G9 230V CL 1CT
Full product code	872790089577300
Order code	925697744201
Material Nr. (12NC)	925697744201
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8727900895773
Numerator - Packs per outer box	100
EAN/UPC - Case	8727900895797

## Halogen Clickline G9

### Dimensional drawing



Product	D (max)	L	C (max)
Halogen MV Click 18W G9 230V CL 1CT	13 mm	21.7 mm	45 mm

