



MASTER TL-D Super 80

TLDRS32W-S83ECO 25PK

The MASTER TL-D Super 80 lamp offers more lumens per watt and better color rendering than TL-D standard colors. Furthermore, it has a lower mercury content. The lamp can be operated in existing TL-D luminaires.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information		Color Rendering Index (Nom)	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]		78
Life 12-Hr Programstart [Hrs]	36000 h	Operating and Electrical	
Life 12-Hr Instant Start [Hrs]	30000 h	Power (Nom)	32 W
Life 3-Hr Program Start [Hrs]	30000 h	Mechanical and Housing	
Life 3-Hr Instant Start [Hrs]	24000 h	Cap-Base Information	Green Cap
Features	ALTO® (ALTO)	Nominal Length (Inch)	48
Footnotes Fluorescent/CFL 1	Circle E- The encircled E means this bulb meets Federal minimum efficiency standards.	Approval and Application	
Light Technical		Energy Saving Product	Energy Saving
Color Code	TL830 [CCT of 3000K (830)]	Picogram Per Lumen Hour	27 pg/lm.h
Luminous Flux (Nom)	2600 lm	Mercury (Hg) Content (Nom)	1.7 mg
Color Designation	TL830	Product Data	
Design Mean Lumens	2470 lm	Full product code	872790091775800
Correlated Color Temperature (Nom)	3000 K	Order product name	TLDRS32W-S83ECO 25PK


MASTER TL-D Super 80

EAN/UPC - Product	8727900917758
Order code	927869773002
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	25

Material Nr. (12NC)	927869773002
Net Weight (Piece)	134.400 g

Dimensional drawing

Product	TLDRS32W-S83ECO 25PK
---------	----------------------



F32T8/830

