



TL-D Standard Colours

TLDRS32W-CO-25

TL-D Standard Colors lamps (tube diameter of 26 mm) create atmospheres from warm white to cool daylight. Lamps with moderate efficacy and color rendering.

Warnings and Safety


- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information		Controls and Dimming	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]	Dimmable	Yes
Life to 50% Failures (Nom)	12000 h		
Light Technical		Mechanical and Housing	
Color Code	33-640	Bulb Shape	T8 [26 mm (T8)]
Luminous Flux (Nom)	2350 lm		
Color Designation	Cool White (CW)	Approval and Application	
Lumen Maintenance 2000 h (Nom)	90 %	Mercury (Hg) Content (Nom)	8.0 mg
Lumen Maintenance 5000 h (Nom)	83 %		
Correlated Color Temperature (Nom)	4100 K	Product Data	
Color Rendering Index (Nom)	60	Full product code	872790091579200
Operating and Electrical		Order product name	TLDRS32W-CO-25
Power (Nom)	32 W	EAN/UPC - Product	8727900915792
Lamp Current (Nom)	0.265 A	Order code	927870003301
Voltage (Nom)	139 V	Numerator - Quantity Per Pack	1
		Numerator - Packs per outer box	25
		Material Nr. (12NC)	927870003301
		Net Weight (Piece)	134.400 g

TL-D Standard Colours

Dimensional drawing



TL-D 32W/33-640

Product	D (max)	A (max)	B (max)	B (min)	C (max)
TLDRS32W-CO-25	28 mm	1199.4 mm	1206.5 mm	1204.1 mm	1213.6 mm

