



TL-D consumer products

TL-D 36W/865 1PP/10

The lamp can be operated in existing TL-D luminaire and is available in a wide range of wattages and colors.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information		Correlated Color Temperature (Nom)	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]		6500 K
Life To 10% Failures (Nom)	12000 h	Luminous Efficacy (rated) (Nom)	84 lm/W
Life to 50% Failures (Nom)	15000 h	Color Rendering Index (Nom)	85
Life to 50% Failures Preheat (Nom)	20000 h	LLMF 2000 h Rated	96 %
LSF 2000 h Rated	99 %	LLMF 4000 h Rated	95 %
LSF 4000 h Rated	99 %	LLMF 6000 h Rated	94 %
LSF 6000 h Rated	99 %	LLMF 8000 h Rated	93 %
LSF 8000 h Rated	99 %	LLMF 12000 h Rated	92 %
LSF 12000 h Rated	89 %	LLMF 16000 h Rated	91 %
LSF 16000 h Rated	33 %	LLMF 20000 h Rated	90 %
LSF 20000 h Rated	2 %		
Light Technical		Operating and Electrical	
Color Code	865 [CCT of 6500K]	Power (Nom)	36.0 W
Luminous Flux (Nom)	3250 lm	Lamp Current (Nom)	0.440 A
Luminous Flux (Rated) (Nom)	3250 lm		
Color Designation	Cool Daylight	Temperature	
		Design Temperature (Nom)	25 °C

TL-D consumer products

Controls and Dimming

Dimmable	Yes
----------	-----

Approval and Application


Energy Efficiency Label (EEL)	A
Mercury (Hg) Content (Nom)	2.0 mg
Energy Consumption kWh/1000 h	42 kWh

Product Data

Full product code	871150095371125
-------------------	-----------------

Order product name	TL-D 36W/865 1PP/10
EAN/UPC - Product	8711500953711
Order code	927921086513
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	927921086513
Net Weight (Piece)	135.000 g
ILCOS Code	FD-36/65/1B-E-G13


Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL-D 36W/865 1PP/10	28 mm	1199.4 mm	1206.5 mm	1204.1 mm	1213.6 mm

TL-D 36W/865

Photometric data





LDPB_TL-D8_865-Spectral power distribution B/W



LDPO_TL-D8_865-Spectral power distribution Colour


TL-D consumer products

Lifetime



LDLE_TL-D8_0001-Life expectancy diagram

LDLE_TL-D8_0002-Life expectancy diagram



LDLM_TL-D8_0001-Lumen maintenance diagram

