



MASTER TL-D HF Super 80

MASTER TL-D HF Super 80 32W/840 SLV/25

The MASTER TL-D HF Super 80 lamp offers more lumens per watt and better color rendering than TL-D standard colors. Furthermore, it has a lower mercury content. The lamp is designed to be operated on special high-frequency electronic ballasts. It is not for general use.

Warnings and Safety

- Special electronic gear must be used
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


General Information		Color Designation	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]	Color Designation	Cool White (CW)
Life to 50% Failures Preheat (Nom)	20000 h	Correlated Color Temperature (Nom)	4000 K
System Description	High Frequency	Luminous Efficacy (rated) (Nom)	100 lm/W
LSF Preheat 2000 h Rated	99 %	Color Rendering Index (Nom)	>80
LSF Preheat 4000 h Rated	99 %	LLMF 2000 h Rated	96 %
LSF Preheat 6000 h Rated	99 %	LLMF 4000 h Rated	95 %
LSF Preheat 8000 h Rated	99 %	LLMF 6000 h Rated	94 %
LSF Preheat 16000 h Rated	95 %	LLMF 8000 h Rated	93 %
LSF Preheat 20000 h Rated	50 %	LLMF 12000 h Rated	92 %
		LLMF 16000 h Rated	91 %
		LLMF 20000 h Rated	90 %
Light Technical		Operating and Electrical	
Color Code	840 [CCT of 4000K]	Power (Nom)	32.0 W
Luminous Flux (Nom)	3200 lm		
Luminous Flux (Rated) (Nom)	3200 lm		

MASTER TL-D HF Super 80

Lamp Current (Nom)	0.255 A
Temperature	
Design Temperature (Nom)	25 °C
Controls and Dimming	
Dimmable	Yes
Approval and Application	
Energy Efficiency Label (EEL)	A+
Mercury (Hg) Content (Nom)	2.0 mg
Energy Consumption kWh/1000 h	38 kWh

Product Data	
Full product code	871150063153440
Order product name	MASTER TL-D HF Super 80 32W/840 SLV/25
EAN/UPC - Product	8711500631534
Order code	927924584023
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	25
Material Nr. (12NC)	927924584023
Net Weight (Piece)	135.000 g
ILCOS Code	FDH-32/40/1B-L/P-G13-26/1200



Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL-D HF Super 80 32W/840 SLV/25	28 mm	1199.4 mm	1206.5 mm	1204.1 mm	1213.6 mm

TL-D HF 32W/840

Photometric data




LDPB_TL-D8HF_840-Spectral power distribution B/W

LDPO_TL-D8HF_840-Spectral power distribution Colour


MASTER TL-D HF Super 80

Lifetime



LDLE_TL-D8HF_0001-Life expectancy diagram

LDLE_TL-D8HF_0002-Life expectancy diagram



LDLM_TL-D8HF_0001-Lumen maintenance diagram

