



T8 Standard

F32T8/TL840/ALTO 25PK

Philips T8 lamps are energy-efficient lighting solutions.

Product data

General information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Life 12-Hr Programstart [Hrs]	24000 h
Life 12-Hr Instant Start [Hrs]	15000 h
Features	ALTO® (ALTO)
Light technical	
Color Code	TL840 [CCT of 4000K (840)]
Luminous Flux (Nom)	2850 lm
Color Designation	TL840
Design Mean Lumens	2705 lm
Correlated Color Temperature (Nom)	4000 K
Color Rendering Index (Nom)	80
Operating and electrical	
Power (Nom)	32 W
Mechanical and housing	
Cap-Base Information	Green Base

Bulb Shape	T8 [26 mm (T8)]
Approval and application	
Energy Saving Product	Energy Saving
Picogram Per Lumen Hour	29.2 pg/lm.h
Mercury (Hg) Content (Nom)	2.0 mg
Product data	
Full product code	871869674549600
Order product name	F32T8/TL840/ALTO 25PK
EAN/UPC - Product	8718696745496
Order code	927925484001
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	25
Material Nr. (12NC)	927925484001
Copy Net Weight (Piece)	0.130 kg

T8 Standard

Dimensional drawing

Product

F32T8/TL840/ALTO 25PK

F32T8/TL840/ALTO 25PK

