



MASTER TL5 High Efficiency

MASTER TL5 HE 14W/830 1SL/20

This TL5 lamp (tube diameter 16 mm) has a high luminous efficacy, resulting in low energy consumption. The High Efficiency TL5 lamp offers excellent lumen maintenance and good color rendering. Application areas are offices, industry, public and governmental buildings, schools, hospitals and indoor sports lighting.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information		Color Designation	
Cap-Base	G5 [G5]		Warm White (WW)
Life to 50% Failures Preheat (Nom)	24000 h	Luminous Efficacy (@ Max Lumen, Rated) (Nom)	96 lm/W
Features	na [Not Applicable]	Correlated Color Temperature (Nom)	3000 K
System Description	High Efficiency	Luminous Efficacy (rated) (Nom)	86 lm/W
LSF Preheat 2000 h Rated	99 %	Color Rendering Index (Max)	85
LSF Preheat 4000 h Rated	99 %	Color Rendering Index (Min)	80
LSF Preheat 6000 h Rated	99 %	Color Rendering Index (Nom)	>80
LSF Preheat 8000 h Rated	99 %	LLMF 2000 h Rated	96 %
LSF Preheat 16000 h Rated	97 %	LLMF 4000 h Rated	95 %
LSF Preheat 20000 h Rated	84 %	LLMF 6000 h Rated	94 %
		LLMF 8000 h Rated	93 %
		LLMF 12000 h Rated	92 %
		LLMF 16000 h Rated	91 %
		LLMF 20000 h Rated	90 %
Light Technical			
Color Code	830 [CCT of 3000K]		
Luminous Flux (Nom)	1350 lm		
Luminous Flux (Rated) (Nom)	1200 lm		

MASTER TL5 High Efficiency

Operating and Electrical	
Power (Nom)	14 W
Lamp Current (Nom)	0.165 A
Temperature	
Design Temperature (Nom)	35 °C
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Cap-Base Information	Green Plate
Approval and Application	
Energy Efficiency Label (EEL)	A+

Mercury (Hg) Content (Nom)	1.4 mg
Energy Consumption kWh/1000 h	15 kWh
Product Data	
Full product code	871150063938705
Order product name	MASTER TL5 HE 14W/830 1SL/20
EAN/UPC - Product	8711500639387
Order code	927926083061
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	20
Material Nr. (12NC)	927926083061
Net Weight (Piece)	52.000 g
ILCOS Code	FDH-14/30/1B-L/P-G5-16/550


Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL5 HE 14W/830 1SL/20	17 mm	549.0 mm	556.1 mm	553.7 mm	563.2 mm

TL5 14W/830/GP HE

Photometric data




LDPB_TL5-HE8_830-Spectral power distribution B/W



LDPO_TL5-HE8_830-Spectral power distribution Colour

MASTER TL5 High Efficiency

Lifetime



LDLE_TL5-HE8_0001-Life expectancy diagram

LDLE_TL5-HE8_0002-Life expectancy diagram



LDLM_TL5-HE8_0001-Lumen maintenance diagram

