



# TL5 Essential HE Super 80

## TL5 Essential 21W/840 1SL/40

Philips TL5 Essential Super80 is a new fluorescent lamp which provides home users and professional end-users an aesthetic miniaturized lighting solution with high reliability at low price.

### Warnings and Safety

- 20,000 hours lifetime (50% survival point, 3 hour cycle) with preheat ballast which is ENEC compliant. Lifetime performance may differ on non-ENEC compliant ballasts.

### Product data


General information		Color Rendering Index (Max)	
Cap-Base	G5 [ G5]	Color Rendering Index (Max)	85
Life to 50% Failures Preheat (Nom)	20000 h	Color Rendering Index (Min)	80
LSF Preheat 2000 h Rated	98 %	Color Rendering Index (Nom)	82
LSF Preheat 4000 h Rated	97 %	LLMF 2000 h Rated	94 %
LSF Preheat 6000 h Rated	95 %	LLMF 4000 h Rated	92 %
LSF Preheat 8000 h Rated	93 %	LLMF 6000 h Rated	91 %
LSF Preheat 16000 h Rated	70 %	LLMF 8000 h Rated	90 %
LSF Preheat 20000 h Rated	50 %	LLMF 12000 h Rated	88 %
		LLMF 16000 h Rated	87 %
		LLMF 20000 h Rated	86 %
Light technical		Operating and electrical	
Color Code	840 [ CCT of 4000K]	Power (Nom)	20.8 W
Luminous Flux (Nom)	2100 lm	Lamp Current (Nom)	0.170 A
Luminous Flux (Rated) (Nom)	1950 lm		
Color Designation	Cool White (CW)		
Luminous Efficacy (@ Max Lumen, Rated) (Nom)	101 lm/W		
Correlated Color Temperature (Nom)	4000 K	Temperature	
Luminous Efficacy (rated) (Nom)	94 lm/W	Design Temperature (Nom)	30 °C

# TL5 Essential HE Super 80

Controls and dimming	
Dimmable	No
Mechanical and housing	
Bulb Shape	T5 [ 16 mm (T5)]
Approval and application	
Mercury (Hg) Content (Nom)	2.0 mg
Product data	
Full product code	871150057039055

Order product name	TL5 Essential 21W/840 1SL/40
EAN/UPC - Product	8711500570390
Order code	927926484058
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	40
Material Nr. (12NC)	927926484058
Net Weight (Piece)	64.000 g


## Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL5 Essential 21W/840 1SL/40	17.0 mm	849.0 mm	856.1 mm	853.7 mm	863.2 mm

TL5 Essential 21W/840 1SL/40

## Photometric data



LDPO\_TL5ESS8\_ESS\_840-Spectral power distribution Colour

## TL5 Essential HE Super 80

