



# MASTER TL5 High Efficiency



## MASTER TL5 HE 28W/840 1SL/20

This TL5 lamp (tube diameter 16 mm) has a high luminous efficacy, resulting in low energy consumption. The High Efficiency TL5 lamp offers excellent lumen maintenance and good color rendering. Application areas are offices, industry, public and governmental buildings, schools, hospitals and indoor sports lighting.

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data

General information		Color Designation	
Cap-Base	G5 [ G5]		Cool White (CW)
Life to 50% Failures Preheat (Nom)	24000 h	Luminous Efficacy (@ Max Lumen, Rated) (Nom)	104 lm/W
Features	na [ Not Applicable]	Correlated Color Temperature (Nom)	4000 K
System Description	High Efficiency	Luminous Efficacy (rated) (Nom)	96 lm/W
LSF Preheat 2000 h Rated	99 %	Color Rendering Index (Max)	85
LSF Preheat 4000 h Rated	99 %	Color Rendering Index (Min)	80
LSF Preheat 6000 h Rated	99 %	Color Rendering Index (Nom)	82
LSF Preheat 8000 h Rated	99 %	LLMF 2000 h Rated	96 %
LSF Preheat 16000 h Rated	97 %	LLMF 4000 h Rated	95 %
LSF Preheat 20000 h Rated	84 %	LLMF 6000 h Rated	94 %
		LLMF 8000 h Rated	93 %
		LLMF 12000 h Rated	92 %
		LLMF 16000 h Rated	91 %
		LLMF 20000 h Rated	90 %
Light technical			
Color Code	840 [ CCT of 4000K]		
Luminous Flux (Nom)	2900 lm		
Luminous Flux (Rated) (Nom)	2675 lm		

# MASTER TL5 High Efficiency

Operating and electrical	
Power (Nom)	27.9 W
Lamp Current (Nom)	0.170 A
Temperature	
Design Temperature (Nom)	35 °C
Controls and dimming	
Dimmable	Yes
Mechanical and housing	
Cap-Base Information	Green Plate
Bulb Shape	T5 [ 16 mm (T5)]
Approval and application	
Energy Efficiency Class	F

Mercury (Hg) Content (Nom)	1.2 mg
Energy Consumption kWh/1000 h	31 kWh
EPREL Registration Number	423537
Product data	
Full product code	871150063948605
Order product name	MASTER TL5 HE 28W/840 1SL/20
EAN/UPC - Product	8711500639486
Order code	927926584061
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	20
Material Nr. (12NC)	927926584061
Net Weight (Piece)	105.800 g
ILCOS Code	FDH-28/40/1B-L/P-G5-16/1150


## Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL5 HE 28W/840 1SL/20	17 mm	1149.0 mm	1156.1 mm	1153.7 mm	1163.2 mm

## MASTER TL5 HE 28W/840 1SL/20

## Photometric data



LDPB\_TL5-HE8\_840-Spectral power distribution B/W



LDPO\_TL5-HE8\_840-Spectral power distribution Colour

# MASTER TL5 High Efficiency

## Lifetime



LDLE\_TL5-HE8\_0001-Life expectancy diagram

LDLE\_TL5-HE8\_0002-Life expectancy diagram



LDLM\_TL5-HE8\_0001-Lumen maintenance diagram

