



MASTER TL5 High Efficiency



MASTER TL5 HE 35W/840 UNP/40

This TL5 lamp (tube diameter 16 mm) has a high luminous efficacy, resulting in low energy consumption. The High Efficiency TL5 lamp offers excellent lumen maintenance and good color rendering. Application areas are offices, industry, public and governmental buildings, schools, hospitals and indoor sports lighting.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General information		Luminous Flux (Rated) (Nom)	
Cap-Base	G5 [G5]		3325 lm
Life to 50% Failures Preheat (Nom)	24000 h	Color Designation	Cool White (CW)
Features	na [Not Applicable]	Luminous Efficacy (@ Max Lumen, Rated) (Nom)	104 lm/W
System Description	High Efficiency	Chromaticity Coordinate X (Nom)	0.38
LSF Preheat 2000 h Rated	99 %	Chromaticity Coordinate Y (Nom)	0.38
LSF Preheat 4000 h Rated	99 %	Correlated Color Temperature (Nom)	4000 K
LSF Preheat 6000 h Rated	99 %	Luminous Efficacy (rated) (Nom)	94 lm/W
LSF Preheat 8000 h Rated	99 %	Color Rendering Index (Max)	85
LSF Preheat 16000 h Rated	97 %	Color Rendering Index (Min)	80
LSF Preheat 20000 h Rated	84 %	Color Rendering Index (Nom)	80
Flux measurement reference	Sphere	LLMF 2000 h Rated	96 %
		LLMF 4000 h Rated	95 %
		LLMF 6000 h Rated	94 %
		LLMF 8000 h Rated	93 %
		LLMF 12000 h Rated	92 %
Light technical			
Color Code	840 [CCT of 4000K]		
Luminous Flux (Nom)	3315 lm		

MASTER TL5 High Efficiency

LLMF 16000 h Rated	91 %
LLMF 20000 h Rated	90 %

Operating and electrical

Power (Nom)	34.9 W
Lamp Current (Nom)	0.175 A

Temperature

Design Temperature (Nom)	35 °C
--------------------------	-------

Controls and dimming

Dimmable	Yes
----------	-----

Mechanical and housing

Cap-Base Information	Green Plate
Bulb Shape	T5 [16 mm (T5)]

Approval and application

Energy Efficiency Class	F
-------------------------	---

Mercury (Hg) Content (Nom)	1.2 mg
Energy Consumption kWh/1000 h	35 kWh
EPREL Registration Number	423542

Product data

Full product code	871150061105555
Order product name	MASTER TL5 HE 35W/840 UNP/40
EAN/UPC - Product	8711500611055
Order code	927927084018
Numerator - Quantity Per Pack	1
Local code description	LAMP FLUOR TUB T5 TL5-35W-HE/840
Numerator - Packs per outer box	40
Material Nr. (12NC)	927927084018
Net Weight (Piece)	127.400 g
ILCOS Code	FDH-35/40/1B-L/P-G5-16/1450


Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL5 HE 35W/840 UNP/40	17 mm	1449.0 mm	1456.1 mm	1453.7 mm	1463.2 mm

MASTER TL5 HE 35W/840 UNP/40

Photometric data



LDPB_TL5-HE8_840-Spectral power distribution B/W



LDPO_TL5-HE8_840-Spectral power distribution Colour

MASTER TL5 High Efficiency

Lifetime



LDLE_TL5-HE8_0001-Life expectancy diagram

LDLE_TL5-HE8_0002-Life expectancy diagram



LDLM_TL5-HE8_0001-Lumen maintenance diagram

