



MASTER TL5 High Output Secura

MASTER TL5 HO Secura 54W/840 UNP/40

This TL5 High Output Secura lamp (tube diameter 16 mm) has a protective coating that keeps glass and lamp components together in the event of accidental breakage. The lamp is easily identifiable by a blue ring at one end. Application areas are all places where glass shatters can disturb operations and can have an impact on product and people safety, e.g. the food and beverage industry. This lamp is compliant with HACCP regulations and supports HACCP certification.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- In order to ensure the integrity of the coating, it is strongly recommended to replace Secura lamps before or at the moment the specified lamp life (50% failures @ 3 hrs switching cycle) is reached.

Product data

General Information		Light Technical	
Cap-Base	G5 [G5]	Color Code	840 [CCT of 4000K]
Life to 50% Failures Preheat (Nom)	30000 h	Luminous Flux (Nom)	4425 lm
System Description	High Output	Luminous Flux (Rated) (Nom)	4500 lm
LSF Preheat 2000 h Rated	99 %	Color Designation	Cool White (CW)
LSF Preheat 4000 h Rated	99 %	Luminous Efficacy (@ Max Lumen, Rated) (Nom)	93 lm/W
LSF Preheat 6000 h Rated	99 %	Chromaticity Coordinate X (Nom)	0.38
LSF Preheat 8000 h Rated	99 %	Chromaticity Coordinate Y (Nom)	0.38
LSF Preheat 16000 h Rated	97 %	Correlated Color Temperature (Nom)	4000 K
LSF Preheat 20000 h Rated	84 %	Luminous Efficacy (rated) (Nom)	83 lm/W
Flux measurement reference	Sphere	Color Rendering Index (Max)	85
		Color Rendering Index (Min)	80

MASTER TL5 High Output Secura

Color Rendering Index (Nom)	80
LLMF 2000 h Rated	96 %
LLMF 4000 h Rated	95 %
LLMF 6000 h Rated	94 %
LLMF 8000 h Rated	93 %
LLMF 12000 h Rated	92 %
LLMF 16000 h Rated	91 %
LLMF 20000 h Rated	90 %

Operating and Electrical

Power (Nom)	53.8 W
Lamp Current (Nom)	0.455 A

Temperature

Design Temperature (Nom)	35 °C
--------------------------	-------

Controls and Dimming

Dimmable	Yes
----------	-----

Mechanical and Housing

Cap-Base Information	Green Plate
Bulb Shape	T5 [16 mm (T5)]


Approval and Application

Energy Efficiency Class	G
Mercury (Hg) Content (Max)	1.4 mg
Mercury (Hg) Content (Nom)	1.4 mg
Energy Consumption kWh/1000 h	54 kWh
EPREL Registration Number	423566

Product Data

Full product code	871150095231855
Order product name	MASTER TL5 HO Secura 54W/840 UNP/40
EAN/UPC - Product	8711500952318
Order code	927929184018
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	40
Material Nr. (12NC)	927929184018
Net Weight (Piece)	143.280 g
ILCOS Code	FDH-54/40/1B-L/P-G5-16/1150

Dimensional drawing





Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL5 HO Secura 54W/840 UNP/40	17 mm	1149.0 mm	1156.1 mm	1153.7 mm	1163.2 mm

TL5 HO Secura 54W/840

MASTER TL5 High Output Secura



Photometric data



LDPB_TL5HO8SE_840-Spectral power distribution B/W


LDPO_TL5HO8SE_840-Spectral power distribution Colour

Lifetime



LDLE_TL5HO8SE_0001-Life expectancy diagram

LDLE_TL5HO8SE_0002-Life expectancy diagram



LDLM_TL5HO8SE_0001-Lumen maintenance diagram

MASTER TL5 High Output Secura

