



TL-D LIFEMAX Super 80

TL-D 36W/865 1SL/25

The TL-D LIFEMAX Super 80 lamp offers more lumens per watt and better color rendering than TL-D standard colors. Furthermore, it has a lower mercury content. The lamp can be operated in existing TL-D luminaires.

Product data

| General Information | |
|------------------------------------|---------------------------------|
| Cap-Base | G13 [Medium Bi-Pin Fluorescent] |
| Life to 50% Failures (Nom) | 15,000 hour(s) |
| Light Technical | |
| Color Code | 865 [CCT of 6500K] |
| Color Designation | Cool Daylight |
| Correlated Color Temperature (Nom) | 6500 K |
| Luminous Efficacy (rated) (Nom) | 85 lm/W |
| Color rendering index (CRI) | 80 |
| Operating and Electrical | |
| Power Consumption | 36 W |
| Lamp Current (Nom) | 0.440 A |
| Voltage (Nom) | 103 V |
| Voltage (Nom) | 103 V |
| Controls and Dimming | |
| Dimmable | Yes |

| Mechanical and Housing | |
|---------------------------------|---------------------|
| Bulb Shape | T8 |
| Approval and Application | |
| Mercury (Hg) Content (Nom) | 2.0 mg |
| Product Data | |
| Order product name | TL-D 36W/865 1SL/25 |
| Full product name | TL-D 36W/865 1SL/25 |
| Full product code | 694793919450600 |
| Order code | 927982286553 |
| Material Nr. (12NC) | 927982286553 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 6947939194506 |
| Numerator - Packs per outer box | 25 |
| EAN/UPC - Case | 6922341996412 |


TL-D LIFEMAX Super 80

Dimensional drawing




| Product | D (max) | A (max) | B (max) | B (min) | C (max) |
|---------------------|---------|------------|------------|------------|------------|
| TL-D 36W/865 1SL/25 | 28 mm | 1,199.4 mm | 1,206.5 mm | 1,204.1 mm | 1,213.6 mm |

Photometric data




Spectral Power Distribution Colour - TL-D 36W/865 1SL/25

Lifetime




Life Expectancy Diagram - TL-D 36W/865 1SL/25



Life Expectancy Diagram - TL-D 36W/865 1SL/25

TL-D LIFEMAX Super 80

Lifetime



Lumen Maintenance Diagram - TL-D 36W/865 1SL/25

