



# MASTER TL-D Xtreme

## MASTER TL-D Xtreme 36W/865 SLV

This MASTER TL-D Xtreme lamp offers extremely long lifetime. This results in extra-low lamp cost over life. It is therefore suitable for places where lamp replacement is expensive, due to high ceilings or disturbance of operations, and applications with long burning cycles, e.g. tunnels, oil rigs, manufacturing lines. It can be operated on existing gear or dedicated HF Xtreme gear.

### Warnings and Safety

- To achieve published lifetimes for 100% operation, do not dim below 30%
- When used on electromagnetic gear, it is strongly recommended to apply only Philips S10 or S10E starters (for 18W types S2 or S2E) to achieve the published lifetimes, and to install new starters when relamping.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data

General Information	
Cap-Base	G13 [ Medium Bi-Pin Fluorescent]
Life to 50% Failures (Nom)	47000 h
Life to 50% Failures Preheat (Nom)	79000 h
LSF 2000 h Rated	100 %
LSF 4000 h Rated	99 %
LSF 6000 h Rated	99 %
LSF 8000 h Rated	99 %
LSF 12000 h Rated	99 %
LSF 16000 h Rated	99 %
LSF 20000 h Rated	99 %
Light Technical	
Color Code	865 [ CCT of 6500K]

Luminous Flux (Nom)	3150 lm
Luminous Flux (Rated) (Nom)	3150 lm
Color Designation	Cool Daylight
Correlated Color Temperature (Nom)	6500 K
Luminous Efficacy (rated) (Nom)	88 lm/W
Color Rendering Index (Nom)	>80
LLMF 2000 h Rated	96 %
LLMF 4000 h Rated	95 %
LLMF 6000 h Rated	94 %
LLMF 8000 h Rated	93 %
LLMF 12000 h Rated	92 %
LLMF 16000 h Rated	91 %
LLMF 20000 h Rated	90 %

# MASTER TL-D Xtreme

## Operating and Electrical

Power (Nom)	36.0 W
Lamp Current (Nom)	0.430 A

## Temperature

Design Temperature (Nom)	25 °C
--------------------------	-------

## Controls and Dimming

Dimmable	Yes
----------	-----

## Approval and Application

Energy Efficiency Label (EEL)	A
Mercury (Hg) Content (Nom)	3.0 mg
Energy Consumption kWh/1000 h	42 kWh

## Product Data


Full product code	871150089277540
Order product name	MASTER TL-D Xtreme 36W/865 SLV
EAN/UPC - Product	8711500892775
Order code	927982386514
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	25
Material Nr. (12NC)	927982386514
Net Weight (Piece)	135.000 g
ILCOS Code	FD-36/65/1B-E-G13

## Dimensional drawing


Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL-D Xtreme 36W/865 SLV	28 mm	1199.4 mm	1206.5 mm	1204.1 mm	1213.6 mm

## TL-D Xtreme 36W/865

## Photometric data




LDPB\_TL-D8LL\_865-Spectral power distribution B/W



LDPO\_TL-D8LL\_865-Spectral power distribution Colour



# MASTER TL-D Xtreme

## Lifetime



LDLE\_TL-D8LL\_0001-Life expectancy diagram

LDLE\_TL-D8LL\_0002-Life expectancy diagram



LDLE\_TL-D8LL\_0003-Life expectancy diagram

LDLM\_TL-D8LL\_0001-Lumen maintenance diagram

