



TL-D LIFEMAX Super 80

TL-D 58W/865 1SL/25

The TL-D LIFEMAX Super 80 lamp offers more lumens per watt and better color rendering than TL-D standard colors. Furthermore, it has a lower mercury content. The lamp can be operated in existing TL-D luminaires.

Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Life To 10% Failures (Nom)	10000 h
Life to 50% Failures (Nom)	15000 h
Life to 50% Failures Preheat (Nom)	20000 h

Light Technical	
Color Code	865 [CCT of 6500K]
Luminous Flux (Rated) (Nom)	4800 lm
Color Designation	Cool Daylight
Lumen Maintenance 2000 h (Nom)	96 %
Lumen Maintenance 5000 h (Nom)	94 %
Correlated Color Temperature (Nom)	6500 K
Luminous Efficacy (rated) (Nom)	82 lm/W
Color Rendering Index (Nom)	80

Operating and Electrical	
Power (Nom)	58.5 W
Lamp Current (Nom)	0.670 A
Voltage (Nom)	111 V

Controls and Dimming	
Dimmable	Yes


Mechanical and Housing	
Cap-Base Information	Green Cap
Bulb Shape	T8 [26 mm (T8)]

Approval and Application	
Mercury (Hg) Content (Nom)	2.0 mg

Product Data	
Full product code	871150028496940
Order product name	TL-D 58W/865 1SL/25
EAN/UPC - Product	8711500284969
Order code	927983286536
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	25
Material Nr. (12NC)	927983286536
Net Weight (Piece)	0.230 kg

TL-D LIFEMAX Super 80


Dimensional drawing




TL-D 58W/865/GC

Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL-D 58W/865 1SL/25	28 mm	1500.0 mm	1507.1 mm	1504.7 mm	1514.2 mm

Photometric data




LDPB_TL-D8G_865-Spectral power distribution B/W




LDPO_TL-D8G_865-Spectral power distribution Colour

Lifetime




LDLE_TL-D8G_0001-Life expectancy diagram



LDLE_TL-D8G_0002-Life expectancy diagram

TL-D LIFEMAX Super 80

Lifetime



LDLM_TL-D8G_0001-Lumen maintenance diagram

