



MASTER TL5 High Output Eco

MASTER TL5 HO Eco 45=49W/830 UNP/40

This extremely efficient TL5 lamp (tube diameter 16 mm) saves considerable energy by simple lamp-for-lamp replacement. The TL5 HO Eco lamp is optimized for installations requiring high light output and offers excellent lumen maintenance and color rendering. Application areas vary from offices and industry to schools and retail environments.

Warnings and Safety

- A reduction in energy consumption is only achieved with current-controlled gear.
- The lamps operate perfectly with power-controlled gear, but in that case the light output can be up to 10% higher.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information		Luminous Flux (Nom)	
Cap-Base	G5 [G5]	Luminous Flux (Rated) (Nom)	4100 lm
Life to 50% Failures Preheat (Nom)	30000 h	Color Designation	Warm White (WW)
Features	na [Not Applicable]	Luminous Efficacy (@ Max Lumen, Rated) (Nom)	108 lm/W
LSF Preheat 2000 h Rated	99 %	Correlated Color Temperature (Nom)	3000 K
LSF Preheat 4000 h Rated	99 %	Luminous Efficacy (rated) (Nom)	92 lm/W
LSF Preheat 6000 h Rated	99 %	Color Rendering Index (Max)	85
LSF Preheat 8000 h Rated	99 %	Color Rendering Index (Min)	80
LSF Preheat 16000 h Rated	99 %	Color Rendering Index (Nom)	82
LSF Preheat 20000 h Rated	94 %	LLMF 2000 h Rated	96 %
Light Technical		LLMF 4000 h Rated	95 %
Color Code	830 [CCT of 3000K]	LLMF 6000 h Rated	94 %

MASTER TL5 High Output Eco

LLMF 8000 h Rated	93 %
LLMF 12000 h Rated	92 %
LLMF 16000 h Rated	91 %
LLMF 20000 h Rated	90 %

Operating and Electrical

Power (Nom)	44.6 W
Lamp Current (Nom)	0.260 A

Temperature

Design Temperature (Nom)	35 °C
--------------------------	-------

Controls and Dimming

Dimmable	Yes
----------	-----

Mechanical and Housing

Bulb Shape	T5 [16 mm (T5)]
------------	------------------

Approval and Application

Mercury (Hg) Content (Nom)	1.4 mg
Energy Consumption kWh/1000 h	50 kWh

Product Data


Full product code	872790082594700
Order product name	MASTER TL5 HO Eco 45=49W/830 UNP/40
EAN/UPC - Product	8711500880062
Order code	927991783031
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	40
Material Nr. (12NC)	927991783031
Net Weight (Piece)	127.400 g
ILCOS Code	FDH-45/30/1B-L/P-G5-16/1450

Dimensional drawing


Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL5 HO Eco 45=49W/830 UNP/40	17 mm	1449.0 mm	1456.1 mm	1453.7 mm	1463.2 mm

TL5 HO Eco 45=49W/830

Photometric data




LDPB_TL5ECO_830-Spectral power distribution B/W



LDPO_TL5ECO_830-Spectral power distribution Colour


MASTER TL5 High Output Eco

Lifetime



LDLE_TL5ECO_0001-Life expectancy diagram

LDLE_TL5ECO_0002-Life expectancy diagram



LDLM_TL5ECO_0001-Lumen maintenance diagram

