



# TL Mini consumer products



## TL Mini 6W/33-640 1PP/10

They come in different wattages and colors with moderate (/33) to good (/827) light quality.

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data

General information	
Cap-Base	G5 [ G5]
Life To 10% Failures (Nom)	5000 h
Life to 50% Failures (Nom)	10000 h
Life to 50% Failures Preheat (Nom)	10000 h
System Description	-
Flux measurement reference	Sphere

Light technical	
Color Code	33-640
Luminous Flux (Nom)	260 lm
Color Designation	Cool White (CW)
Lumen Maintenance 10000 h (Nom)	58 %
Lumen Maintenance 2000 h (Nom)	75 %
Lumen Maintenance 5000 h (Nom)	70 %
Chromaticity Coordinate X (Nom)	0.38
Chromaticity Coordinate Y (Nom)	0.38
Correlated Color Temperature (Nom)	4000 K

Luminous Efficacy (rated) (Nom)	43 lm/W
Color Rendering Index (Nom)	59

Operating and electrical	
Power (Nom)	6.0 W
Lamp Current (Nom)	0.160 A
Voltage (Nom)	42 V

Controls and dimming	
Dimmable	Yes

Mechanical and housing	
Bulb Shape	T5 [ 16 mm (T5)]


Approval and application	
Energy Efficiency Class	G
Mercury (Hg) Content (Max)	2.5 mg
Mercury (Hg) Content (Nom)	4.4 mg

## TL Mini consumer products

Energy Consumption kWh/1000 h	6 kWh
EPREL Registration Number	423487
<b>Product data</b>	
Full product code	871150062693625
Order product name	TL Mini 6W/33-640 1PP/10
EAN/UPC - Product	8711500626936
Order code	928000503313

Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	928000503313
Net Weight (Piece)	21.000 g
ILCOS Code	FD-6/41/2B-E-G5


## Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL Mini 6W/33-640 1PP/10	16 mm	212.1 mm	219.2 mm	216.8 mm	226.3 mm

TL Mini 6W/33-640 1PP/10

## Photometric data



LDPB\_TL-MINI\_33-640-Spectral power distribution B/W



LDPO\_TL-MINI\_33-640-Spectral power distribution Colour

