



TL Mini Standard Colours



TL Mini 8W/54-765 FAM/10X25BOX

This TL Miniature lamp (tube diameter 16 mm) is a lamp with small dimensions, which enables system miniaturization and offers the possibility of operation on low-voltage DC supply. It is ideal for applications where space is limited but where color rendering and efficacy are not the most important factors, such as orientation, signage and emergency lighting.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General information		Operating and electrical	
Cap-Base	G5 [G5]	Chromaticity Coordinate X (Nom)	0.313
Life To 10% Failures (Nom)	5000 h	Chromaticity Coordinate Y (Nom)	0.337
Life to 50% Failures (Nom)	10000 h	Correlated Color Temperature (Nom)	6500 K
Life to 50% Failures Preheat (Nom)	10000 h	Luminous Efficacy (rated) (Nom)	48 lm/W
System Description	-	Color Rendering Index (Nom)	72
Flux measurement reference	Sphere		
Light technical		Controls and dimming	
Color Code	54-765	Dimmable	Yes
Luminous Flux (Nom)	335 lm		
Color Designation	Cool Daylight		
Lumen Maintenance 10000 h (Nom)	58 %		
Lumen Maintenance 2000 h (Nom)	80 %		
Lumen Maintenance 5000 h (Nom)	70 %		

TL Mini Standard Colours

Mechanical and housing

Bulb Shape T5 [16 mm (T5)]

Approval and application


Energy Efficiency Class G
 Mercury (Hg) Content (Max) 2.5 mg
 Mercury (Hg) Content (Nom) 4.4 mg
 Energy Consumption kWh/1000 h 8 kWh
 EPREL Registration Number 423492

Product data

Full product code 871150071628627

Order product name	TL Mini 8W/54-765 FAM/10X25BOX
EAN/UPC - Product	8711500716286
Order code	928001005440
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	250
Material Nr. (12NC)	928001005440
Net Weight (Piece)	27.000 g
ILCOS Code	FD-8/62/2A-E-G5


Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL Mini 8W/54-765 FAM/10X25BOX	16 mm	288.3 mm	295.4 mm	293.0 mm	302.5 mm

TL Mini 8W/54-765 FAM/10X25BOX

Photometric data



LDPB_TL-MINI_54-765-Spectral power distribution B/W



LDPO_TL-MINI_54-765-Spectral power distribution Colour

TL Mini Standard Colours

