



MASTER TL Mini Super 80



MASTER TL Mini Super 80 8W/830 FAM/10X25BOX

This TL Miniature lamp (tube diameter 16 mm) is a lamp with small dimensions, which enables system miniaturization and offers the possibility of operation on low-voltage DC supply. It is ideal for applications where better color rendering and efficacy (than standard colors) are required and where space is limited, e.g. halls, staircase lighting in apartment buildings, built into furniture, mirror and cupboard lighting, signage and emergency lighting.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General information

Cap-Base	G5 [G5]
Life To 10% Failures (Nom)	5000 h
Life to 50% Failures (Nom)	10000 h
Life to 50% Failures Preheat (Nom)	10000 h
Flux measurement reference	Sphere

Light technical

Color Code	830 [CCT of 3000K]
Luminous Flux (Nom)	450 lm
Color Designation	Warm White (WW)
Lumen Maintenance 10000 h (Nom)	71 %

Lumen Maintenance 2000 h (Nom)	85 %
Lumen Maintenance 5000 h (Nom)	77 %
Chromaticity Coordinate X (Nom)	0.44
Chromaticity Coordinate Y (Nom)	0.403
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	59 lm/W
Color Rendering Index (Nom)	82

Operating and electrical

Power (Nom)	7.1 W
Lamp Current (Nom)	0.145 A


MASTER TL Mini Super 80

Voltage (Nom)	56 V
Controls and dimming	
Dimmable	Yes
Mechanical and housing	
Bulb Shape	T5 [16 mm (T5)]
Approval and application	
Energy Efficiency Class	G
Mercury (Hg) Content (Max)	2.5 mg
Mercury (Hg) Content (Nom)	3.0 mg
Energy Consumption kWh/1000 h	8 kWh
EPREL Registration Number	423495

Product data

Full product code	871150071638527
Order product name	MASTER TL Mini Super 80 8W/830 FAM/10X25BOX
EAN/UPC - Product	8711500716385
Order code	928001008350
Numerator - Quantity Per Pack	1
Local code description	4922369
Numerator - Packs per outer box	250
Material Nr. (12NC)	928001008350
Net Weight (Piece)	27.000 g
ILCOS Code	FD-8/30/1B-E-G5


Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL Mini Super 80 8W/830 FAM/10X25BOX	16 mm	288.3 mm	295.4 mm	293.0 mm	302.5 mm

MASTER TL Mini Super 80 8W/830 FAM/10X25BOX

Photometric data



LDPB_TL8MINI_830-Spectral power distribution B/W

LDPO_TL8MINI_830-Spectral power distribution Colour

MASTER TL Mini Super 80

