



MASTER TL-D Super 80



MASTER TL-D Super 80 14W/840 SLV/25

The MASTER TL-D Super 80 lamp offers more lumens per watt and better color rendering than TL-D standard colors. Furthermore, it has a lower mercury content. The lamp can be operated in existing TL-D luminaires.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


General Information		Luminous Flux (Rated) (Nom)	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]	Luminous Flux (Rated) (Nom)	860 lm
Life To 10% Failures (Nom)	12000 h	Color Designation	Cool Daylight
Life to 50% Failures (Nom)	15000 h	Chromaticity Coordinate X (Nom)	0.38
Life to 50% Failures Preheat (Nom)	20000 h	Chromaticity Coordinate Y (Nom)	0.38
LSF 2000 h Rated	99 %	Correlated Color Temperature (Nom)	4000 K
LSF 4000 h Rated	99 %	Luminous Efficacy (rated) (Nom)	63 lm/W
LSF 6000 h Rated	99 %	Color Rendering Index (Nom)	83
LSF 8000 h Rated	99 %	LLMF 2000 h Rated	96 %
LSF 12000 h Rated	89 %	LLMF 4000 h Rated	95 %
LSF 16000 h Rated	33 %	LLMF 6000 h Rated	94 %
LSF 20000 h Rated	2 %	LLMF 8000 h Rated	93 %
Flux measurement reference	Sphere	LLMF 12000 h Rated	92 %
		LLMF 16000 h Rated	91 %
		LLMF 20000 h Rated	90 %
Light Technical		Operating and Electrical	
Color Code	840 [CCT of 4000K]	Power (Nom)	14.2 W
Luminous Flux (Nom)	860 lm		

MASTER TL-D Super 80

Lamp Current (Nom)	0.380 A
Temperature	
Design Temperature (Nom)	25 °C
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	T8 [26 mm (T8)]
Approval and Application	
Energy Efficiency Class	G
Mercury (Hg) Content (Max)	2 mg
Mercury (Hg) Content (Nom)	2 mg

Energy Consumption kWh/1000 h	15 kWh
EPREL Registration Number	423504
Product Data	
Full product code	871150095381040
Order product name	MASTER TL-D Super 80 14W/840 SLV/25
EAN/UPC - Product	8711500953810
Order code	928024384001
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	25
Material Nr. (12NC)	928024384001
Net Weight (Piece)	42.800 g
ILCOS Code	FD-14/40/1B-E-G13


Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL-D Super 80 14W/840 SLV/25	28 mm	361.2 mm	368.3 mm	365.9 mm	375.4 mm

TL-D 14W/840

Photometric data



LDPB_TL-D8_840_0001-Spectral power distribution B/W



LDPO_TL-D8_840_0001-Spectral power distribution Colour

MASTER TL-D Super 80

Lifetime



LDLE_TL-D8_0001-Life expectancy diagram

LDLE_TL-D8_0002-Life expectancy diagram



LDLM_TL-D8_0001-Lumen maintenance diagram

