



# TL-D Standard Colours

## TL-D 30W/54-765 1SL/25

TL-D Standard Colors lamps (tube diameter of 26 mm) create atmospheres from warm white to cool daylight. Lamps with moderate efficacy and color rendering.

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data

| General information        |                                  |
|----------------------------|----------------------------------|
| Cap-Base                   | G13 [ Medium Bi-Pin Fluorescent] |
| Life To 10% Failures (Nom) | 10000 h                          |
| Life to 50% Failures (Nom) | 13000 h                          |

| Light technical                    |               |
|------------------------------------|---------------|
| Color Code                         | 54-765        |
| Luminous Flux (Nom)                | 1825 lm       |
| Color Designation                  | Cool Daylight |
| Lumen Maintenance 10000 h (Nom)    | 75 %          |
| Lumen Maintenance 2000 h (Nom)     | 90 %          |
| Lumen Maintenance 5000 h (Nom)     | 80 %          |
| Correlated Color Temperature (Nom) | 6200 K        |
| Color Rendering Index (Nom)        | 72            |

| Operating and electrical |         |
|--------------------------|---------|
| Power (Nom)              | 30.0 W  |
| Lamp Current (Nom)       | 0.360 A |

|               |      |
|---------------|------|
| Voltage (Nom) | 98 V |
|---------------|------|

| Controls and dimming |     |
|----------------------|-----|
| Dimmable             | Yes |

| Mechanical and housing |                  |
|------------------------|------------------|
| Bulb Shape             | T8 [ 26 mm (T8)] |

| Approval and application      |        |
|-------------------------------|--------|
| Mercury (Hg) Content (Nom)    | 5.0 mg |
| Energy Consumption kWh/1000 h | 36 kWh |


| Product data                  |                        |
|-------------------------------|------------------------|
| Full product code             | 871869648774700        |
| Order product name            | TL-D 30W/54-765 1SL/25 |
| EAN/UPC - Product             | 8718696487747          |
| Order code                    | 928025405451           |
| Numerator - Quantity Per Pack | 1                      |

# TL-D Standard Colours

|                                 |              |
|---------------------------------|--------------|
| Numerator - Packs per outer box | 25           |
| Material Nr. (12NC)             | 928025405451 |
| Net Weight (Piece)              | 148.900 g    |

|            |                   |
|------------|-------------------|
| ILCOS Code | FD-30/62/2A-E-G13 |
|------------|-------------------|


## Dimensional drawing




TL-D 30W/54-765 1SL/25

| Product                | D (max) | A (max)  | B (max)  | B (min)  | C (max)  |
|------------------------|---------|----------|----------|----------|----------|
| TL-D 30W/54-765 1SL/25 | 28 mm   | 894.6 mm | 901.7 mm | 899.3 mm | 908.8 mm |

## Photometric data




LDPB\_TL-DSTD\_54-765-Spectral power distribution B/W




LDPO\_TL-DSTD\_54-765-Spectral power distribution Colour

## Lifetime




LDLE\_TL-DSTD\_0001-Life expectancy diagram



LDLE\_TL-DSTD\_0002-Life expectancy diagram

## TL-D Standard Colours

### Lifetime



LDLM\_TL-DSTD\_0001-Lumen maintenance diagram

