



TL-D Standard Colours

TLD 30W STANDARD 25PCS

TL-D Standard Colors lamps (tube diameter of 26 mm) create atmospheres from warm white to cool daylight. Lamps with moderate efficacy and color rendering.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


General Information		Voltage (Nom)	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]	98 V	
Life To 10% Failures (Nom)	10000 h	Controls and Dimming	
Life to 50% Failures (Nom)	13000 h	Dimmable	Yes
Light Technical		Mechanical and Housing	
Color Code	75	Bulb Shape	T8 [26 mm (T8)]
Luminous Flux (Nom)	1310 lm	Approval and Application	
Color Designation	Daylight	Mercury (Hg) Content (Nom)	8.0 mg
Lumen Maintenance 2000 h (Nom)	90 %	Product Data	
Lumen Maintenance 5000 h (Nom)	83 %	Full product code	872790091804500
Correlated Color Temperature (Nom)	5000 K	Order product name	TLD 30W STANDARD 25PCS
Color Rendering Index (Nom)	70	EAN/UPC - Product	8727900918045
Operating and Electrical		Order code	928025407548
Power (Nom)	30 W	Numerator - Quantity Per Pack	1
Lamp Current (Nom)	0.360 A	Numerator - Packs per outer box	25

TL-D Standard Colours

Material Nr. (12NC) 928025407548

Net Weight (Piece) 108.600 g

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
TLD 30W STANDARD 25PCS	28 mm	894.6 mm	901.7 mm	899.3 mm	908.8 mm

