



# MASTER TL-E Circular Super 80



## TL-E 32W/830 1CT/12

This circular TL lamp (tube diameter 29 mm) enables omni-directional light distribution. It is suitable for use in a wide range of luminaires for various purposes, including decorative ones, in 'human' applications such as schools, offices, shops and homes, and for lighting of residential areas.

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data

General Information		Correlated Color Temperature (Nom)	
Cap-Base	G10Q [ G10q]		3000 K
Life to 50% Failures (Nom)	13000 h	Luminous Efficacy (rated) (Nom)	74 lm/W
LSF 2000 h Rated	98 %	Color Rendering Index (Nom)	80
LSF 4000 h Rated	77 %	LLMF 2000 h Rated	84 %
LSF 6000 h Rated	60 %	LLMF 4000 h Rated	79 %
LSF 8000 h Rated	45 %	LLMF 6000 h Rated	75 %
Flux measurement reference	Sphere	LLMF 8000 h Rated	73 %
Light Technical		Operating and Electrical	
Color Code	830 [ CCT of 3000K]	Power (Nom)	32.8 W
Luminous Flux (Nom)	2375 lm	Lamp Current (Nom)	0.450 A
Luminous Flux (Rated) (Nom)	2375 lm	Voltage (Nom)	81 V
Color Designation	Warm White (WW)		
Chromaticity Coordinate X (Nom)	0.44	Temperature	
Chromaticity Coordinate Y (Nom)	0.403	Design Temperature (Nom)	25 °C

# MASTER TL-E Circular Super 80

## Controls and Dimming

Dimmable	Yes
----------	-----

## Mechanical and Housing

Bulb Shape	C-T9 [ C-T9 29 mm]
------------	--------------------


## Approval and Application

Energy Efficiency Class	G
Mercury (Hg) Content (Max)	8 mg
Mercury (Hg) Content (Nom)	8 mg
Energy Consumption kWh/1000 h	33 kWh
EPREL Registration Number	423508

## Product Data

Full product code	871150055967815
Order product name	TL-E 32W/830 1CT/12
EAN/UPC - Product	8711500559678
Order code	928026383070
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	12
Material Nr. (12NC)	928026383070
Net Weight (Piece)	0.180 kg
ILCOS Code	FSC-32/30/1B-E-G10q-29/299


## Dimensional drawing



TL-E 32W/830

Product	D (max)	D (min)	E (min)	E (max)	I (min)	I (max)
TL-E 32W/830 1CT/12	30.9 mm	27.1 mm	299.0 mm	303.5 mm	241.0 mm	246.0 mm

## Photometric data



LDPB\_TL-E8\_830-Spectral power distribution B/W

LDPO\_TL-E8\_830-Spectral power distribution Colour

## MASTER TL-E Circular Super 80

