



TL-D Standard Colours

TL-D 18W/33-640 UNP/25

TL-D Standard Colors lamps (tube diameter of 26 mm) create atmospheres from warm white to cool daylight. Lamps with moderate efficacy and color rendering.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


General information		Voltage (Nom)	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]	59 V	
Life To 10% Failures (Nom)	10000 h	Controls and dimming	
Life to 50% Failures (Nom)	13000 h	Dimmable	Yes
Light technical		Mechanical and housing	
Color Code	33-640	Bulb Shape	T8 [26 mm (T8)]
Luminous Flux (Nom)	1200 lm	Approval and application	
Color Designation	Cool White (CW)	Mercury (Hg) Content (Nom)	5.0 mg
Lumen Maintenance 10000 h (Nom)	75 %	Energy Consumption kWh/1000 h	22 kWh
Lumen Maintenance 2000 h (Nom)	90 %	Product data	
Lumen Maintenance 5000 h (Nom)	80 %	Full product code	871150063007000
Correlated Color Temperature (Nom)	4100 K	Order product name	TL-D 18W/33-640 UNP/25
Color Rendering Index (Nom)	63	EAN/UPC - Product	8711500630070
Operating and electrical		Order code	928048003384
Power (Nom)	18.0 W	Numerator - Quantity Per Pack	1
Lamp Current (Nom)	0.360 A		

TL-D Standard Colours

Numerator - Packs per outer box	25
Material Nr. (12NC)	928048003384
Net Weight (Piece)	0.070 kg

ILCOS Code	FD-18/41/2B-E-G13
------------	-------------------


Dimensional drawing



TL-D 18W/33-640 UNP/25

Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL-D 18W/33-640 UNP/25	28 mm	589.8 mm	596.9 mm	594.5 mm	604 mm


Photometric data




LDPB_TL-DSTD_33-640_0001-Spectral power distribution B/W

LDPO_TL-DSTD_33-640_0001-Spectral power distribution Colour

Lifetime



LDLE_TL-DSTD_0001-Life expectancy diagram



LDLE_TL-DSTD_0002-Life expectancy diagram

TL-D Standard Colours

Lifetime



LDLM_TL-DSTD_0001-Lumen maintenance diagram

