



TL-D Standard Colours

TL-D 58W/54-765 1SL/25

TL-D Standard Colors lamps (tube diameter of 26 mm) create atmospheres from warm white to cool daylight. Lamps with moderate efficacy and color rendering.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


Product data

General Information		Voltage (Nom)	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]		111 V
Life To 10% Failures (Nom)	10000 h	Controls and Dimming	
Life to 50% Failures (Nom)	13000 h	Dimmable	Yes
Light Technical		Approval and Application	
Color Code	54-765	Energy Efficiency Label (EEL)	A
Luminous Flux (Nom)	4000 lm	Mercury (Hg) Content (Nom)	8.0 mg
Color Designation	Cool Daylight	Energy Consumption kWh/1000 h	68 kWh
Lumen Maintenance 10000 h (Nom)	75 %	Product Data	
Lumen Maintenance 2000 h (Nom)	90 %	Full product code	872790081590000
Lumen Maintenance 5000 h (Nom)	80 %	Order product name	TL-D 58W/54-765 1SL/25
Correlated Color Temperature (Nom)	6200 K	EAN/UPC - Product	8727900815900
Color Rendering Index (Nom)	72	Order code	928049005451
Operating and Electrical		Numerator - Quantity Per Pack	1
Power (Nom)	58.5 W	Numerator - Packs per outer box	25
Lamp Current (Nom)	0.670 A	Material Nr. (12NC)	928049005451

TL-D Standard Colours

Net Weight (Piece)	167.000 g
ILCOS Code	FD-58/62/2A-E-G13


Dimensional drawing




TL-D 58W/54-765

Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL-D 58W/54-765 1SL/25	28 mm	1500.0 mm	1507.1 mm	1504.7 mm	1514.2 mm

Photometric data




LDPB_TL-DSTD_54-765-Spectral power distribution B/W




LDPO_TL-DSTD_54-765-Spectral power distribution Colour

Lifetime




LDLE_TL-DSTD_0001-Life expectancy diagram



LDLE_TL-DSTD_0002-Life expectancy diagram

TL-D Standard Colours

Lifetime



LDLM_TL-DSTD_0001-Lumen maintenance diagram

