



# TL-D Standard Colours

## TL-D 58W/54-765 1SL/25

TL-D Standard Colors lamps (tube diameter of 26 mm) create atmospheres from warm white to cool daylight. Lamps with moderate efficacy and color rendering.

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data


<b>General information</b>		<b>Voltage (Nom)</b>		111 V	
Cap-Base	G13 [ Medium Bi-Pin Fluorescent]	<b>Controls and dimming</b>			
Life To 10% Failures (Nom)	10000 h	Dimmable	Yes		
Life to 50% Failures (Nom)	13000 h	<b>Mechanical and housing</b>			
<b>Light technical</b>		Bulb Shape	T8 [ 26 mm (T8)]		
Color Code	54-765	<b>Approval and application</b>			
Luminous Flux (Nom)	4000 lm	Mercury (Hg) Content (Nom)	5.0 mg		
Color Designation	Cool Daylight	Energy Consumption kWh/1000 h	68 kWh		
Lumen Maintenance 10000 h (Nom)	75 %	<b>Product data</b>			
Lumen Maintenance 2000 h (Nom)	90 %	Full product code	872790081590000		
Lumen Maintenance 5000 h (Nom)	80 %	Order product name	TL-D 58W/54-765 1SL/25		
Correlated Color Temperature (Nom)	6200 K	EAN/UPC - Product	8727900815900		
Color Rendering Index (Nom)	72	Order code	928049005451		
<b>Operating and electrical</b>		Numerator - Quantity Per Pack	1		
Power (Nom)	58.5 W				
Lamp Current (Nom)	0.670 A				

# TL-D Standard Colours

Numerator - Packs per outer box	25
Material Nr. (12NC)	928049005451
Net Weight (Piece)	167.000 g

ILCOS Code	FD-58/62/2A-E-G13
------------	-------------------


## Dimensional drawing




TL-D 58W/54-765 1SL/25

Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL-D 58W/54-765 1SL/25	28 mm	1500.0 mm	1507.1 mm	1504.7 mm	1514.2 mm

## Photometric data




LDPB\_TL-DSTD\_54-765-Spectral power distribution B/W




LDPO\_TL-DSTD\_54-765-Spectral power distribution Colour

## Lifetime



LDLE\_TL-DSTD\_0001-Life expectancy diagram



LDLE\_TL-DSTD\_0002-Life expectancy diagram

## TL-D Standard Colours

### Lifetime



LDLM\_TL-DSTD\_0001-Lumen maintenance diagram

