



TL-D Standard Colours

TL-D 58W/54 1SL/25

TL-D Standard Colors lamps (tube diameter of 26 mm) create atmospheres from warm white to cool daylight. Lamps with moderate efficacy and color rendering.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

| General Information | |
|----------------------------|----------------------------------|
| Cap-Base | G13 [Medium Bi-Pin Fluorescent] |
| Life To 10% Failures (Nom) | 10000 h |
| Life to 50% Failures (Nom) | 13000 h |

| Light Technical | |
|------------------------------------|---------------|
| Color Code | 54-765 |
| Luminous Flux (Nom) | 4000 lm |
| Color Designation | Cool Daylight |
| Lumen Maintenance 10000 h (Nom) | 75 % |
| Lumen Maintenance 2000 h (Nom) | 90 % |
| Lumen Maintenance 5000 h (Nom) | 80 % |
| Correlated Color Temperature (Nom) | 6200 K |
| Color Rendering Index (Nom) | 72 |

| Operating and Electrical | |
|--------------------------|---------|
| Power (Nom) | 58.5 W |
| Lamp Current (Nom) | 0.670 A |

| Voltage (Nom) | |
|---------------|-------|
| Voltage (Nom) | 111 V |

| Controls and Dimming | |
|----------------------|-----|
| Dimmable | Yes |

| Mechanical and Housing | |
|------------------------|------------------|
| Bulb Shape | T8 [26 mm (T8)] |

| Approval and Application | |
|-------------------------------|--------|
| Mercury (Hg) Content (Nom) | 8.0 mg |
| Energy Consumption kWh/1000 h | 68 kWh |


| Product Data | |
|-------------------------------|--------------------|
| Full product code | 872790091864900 |
| Order product name | TL-D 58W/54 1SL/25 |
| EAN/UPC - Product | 8727900918649 |
| Order code | 928049005481 |
| Numerator - Quantity Per Pack | 1 |

TL-D Standard Colours

| | |
|---------------------------------|--------------|
| Numerator - Packs per outer box | 25 |
| Material Nr. (12NC) | 928049005481 |
| Net Weight (Piece) | 167.000 g |

| | |
|------------|-------------------|
| ILCOS Code | FD-58/62/2A-E-G13 |
|------------|-------------------|


Dimensional drawing




TL-D 58W/54-765

| Product | D (max) | A (max) | B (max) | B (min) | C (max) |
|--------------------|---------|-----------|-----------|-----------|-----------|
| TL-D 58W/54 1SL/25 | 28 mm | 1500.0 mm | 1507.1 mm | 1504.7 mm | 1514.2 mm |

Photometric data




LDPB_TL-DSTD_54-765-Spectral power distribution B/W




LDPO_TL-DSTD_54-765-Spectral power distribution Colour

Lifetime



LDLE_TL-DSTD_0001-Life expectancy diagram



LDLE_TL-DSTD_0002-Life expectancy diagram

TL-D Standard Colours

Lifetime



LDLM_TL-DSTD_0001-Lumen maintenance diagram

