



MASTER LED candles and lusters

MASTER LEDcandle DT 4-25W E14 B38 CL

Delivering incandescent-like sparkling light effects, MASTER LED candles and lusters are ideal for general and decorative lighting in the hospitality industry as well as in home environments. Mounted in full view in chandeliers, wall scones or modern luminaires, the clear or frosted glass candles and lusters fit all existing fixtures with an E14, B15, B22 or E27 socket, and enhance the aesthetic appeal of the chandelier or luminaire both when on and off, with their unique, eye-catching lens design. They produce a beautiful sparkling warm light that delivers huge energy savings and minimizes maintenance cost.

Product data

General Information		Operating and Electrical	
Cap-Base	E14 [E14]	Input Frequency	50 to 60 Hz
EU RoHS compliant	Yes	Power (Nom)	4 W
Nominal Lifetime (Nom)	25000 h	Lamp Current (Nom)	25 mA
Switching Cycle	50000X	Wattage Equivalent	25 W
Technical Type	4-25W	Starting Time (Nom)	0.5 s
		Warm Up Time to 60% Light (Nom)	instant full light
Light Technical		Power Factor (Nom)	0.7
Color Code	822-827 [tunable warm white]	Voltage (Nom)	220-240 V
Luminous Flux (Nom)	250 lm		
Color Designation	Warm White (WW)	Temperature	
Correlated Color Temperature (Nom)	- K	T-Case Maximum (Nom)	85 °C
Luminous Efficacy (rated) (Nom)	65 lm/W		
Color Consistency	<6	Controls and Dimming	
Color Rendering Index (Nom)	80	Dimmable	Yes
LLMF At End Of Nominal Lifetime (Nom)	70 %		

MASTER LED candles and lusters

Mechanical and Housing

Bulb Finish	Clear
Bulb Shape	B38

Approval and Application

Suitable For Accent Lighting	No
Energy Consumption kWh/1000 h	4 kWh

Product Data

Full product code	871869645368100
-------------------	-----------------

Order product name	MASTER LEDcandle DT 4-25W E14 B38 CL
EAN/UPC - Product	8718696453681
Order code	929001139802
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	929001139802
Net Weight (Piece)	0.063 kg

Dimensional drawing



Product	D	C
MASTER LEDcandle DT 4-25W E14 B38 CL	38 mm	113 mm

LED DT 4-25W E14 2200-2700K B38 CL

Photometric data

